


Guided drive DGRC-GF-40-80-PA

Part number: 8218221

FESTO



[PDF](#) General operating condition

Data sheet

Feature	Value
Distance from centre of gravity of load to yoke plate xs	50 mm
Stroke	80 mm
Piston diameter	40 mm
Operating mode, drive unit	Yoke
Cushioning	Elastic cushioning rings/plates at both ends
Mounting position	Any
Guide	Plain-bearing guide
Design	Guidance
Position detection	Via proximity switch
Symbol	00991737
Protection against torque/guide	Guide rod with yoke
Operating pressure	0.15 MPa ... 1 MPa
Operating pressure	1.5 bar ... 10 bar
Max. speed	0.8 m/s
Mode of operation	Double-acting
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Corrosion resistance class CRC	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Ambient temperature	-10 °C ... 60 °C
Impact energy in end positions	0.7 J
Max. force Fy	1057 N
Max. force Fy static	1057 N
Max. force Fz	1057 N
Max. force Fz static	1057 N
Max. moment Mx	44.39 Nm
Max. torque Mx static	44.39 Nm
Max. moment My	31.18 Nm
Max. torque My static	31.18 Nm
Max. moment Mz	31.18 Nm
Max. torque Mz static	31.18 Nm
Max. permissible torque load Mx as a function of stroke	8.22 Nm
Max. effective load dependent upon stroke at defined distance xs	147.9 N
Theoretical force at 0.6 MPa (6 bar, 87 psi), return stroke	686 N

Feature	Value
Theoretical force at 0.6 MPa (6 bar, 87 psi), advance stroke	754 N
Torsional backlash	0.035 deg
Moving mass	996.3 g
Product weight	1888.3 g
Basic weight for 0 mm stroke	892 g
Centre of gravity of moving mass as a function of stroke	66.6 mm
Pneumatic connection	G1/8
Note on materials	RoHS compliant
Material cover	Wrought aluminium alloy
Material seals	NBR
Material dynamic seals	TPE-U(PU)
Material end plate	Anodised wrought aluminium alloy
Material guide rod	High-alloy steel
Material housing	Anodised wrought aluminium alloy
Material piston rod	High-alloy steel