



All MCON Receptacle and Tab (64)

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

| | |
|-----------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU | Compliant |
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUN 2018 (191) Does not contain REACH SVHC |
| Halogen Content | Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free |
| Solder Process Capability | Not applicable for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #DT06-2S-P060
PLG, 2P, BLK, BUSBAR 1X2, NICKEL

TE Part #2297813-2
BASE ASSY, 38 POSN ISO FUSE AND RELAY

TE Part #HC5956
BATT.LEAD 90 DEG 70MM+VE.

TE Part #CAR2PC68-001
CAR PLUG DIN9680 2way, IP68

TE Part #K1128688
Battery Disconnecter 35-411-130-R-900

TE Part #DARS24296-000A3
CAR PIN STANDARD CONT. #5, silver plated

TE Part #SRK-PC-080-35-601
PIN, SOLID, SIZE M8, 35mm2, AG

TE Part #DTSK06-1-08SB
PLUG, INLINE, KEY B

TE Part #K1012918
Relay 26-70-04

TE Part #HC5957
BATT.LEAD 90 DEG 70MM-VE.

Documents

Product Drawings
MCON 1.2 LL REC SWS AG
German

CAD Files
Customer View Model
ENG_CVM_CVM_1452671-3_B.2d_dxf.zip
English
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1452671-3_B.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1452671-3_B.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications



Application Specification

German

Application Specification

English

Application Specification

English