

## Description

CONDUCTIVE CASTOR WITH BOLT HOLE, GREY RUBBER 100MM


## Part Number

Swivel  
DP30A100-272L

Swivel and brake  
DP30D100-272L



	Swivel	Swivel+brake
Wheel Diameter ØD	100 mm	
Overall Height H	134 mm ±1	
Fixing Hole size	12 mm±1	
Center Hole	12,2 mm±1	
Offset F ±1	\	36 mm
Width of Tread	29 mm±0,5	
Hardness of tread	shore A ± 93	
Load capacity	80 Kg	
Weight	0,44 kg	0,5 kg
Temperature	- 5 / + 50 °C	



### Castor Assembly :

Zinc-plated steel. Swivel on two rows of balls.  
Fastening by bolt hole.  
Total lock. Plastic pedal.

### Wheel :

Light grey polypropylene Wheel centre made from electroconductive materials.  
Tread : Dark grey Thermoplastic tyre made from electroconductive materials.  
Plain bearing.

### Features :

Low starting effort.  
Bonded Rubber, non marking.  
Protects sensitive goods and users from electric shocks (electrostatic discharges).  
Conductive casters compliant with ISO 22877.  
Electrical resistance < 100000 ohms.  
For use on trolleys or sensitive devices in laboratories, medical units, hospitals, electrical and electronic factories, explosion hazard areas....