

Features

- High EMC shielding
- Corrosion resistant
- High flexibility

RS PRO Tinned Copper Braid

36 x 7 x 0,20 mm / 7,88 mm², 100 m

RS Stock No.: 534-060



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

The tinned copper shielding braid from RS provides a flexible and robust solution for electromagnetic shielding. The tinned copper braid ensures high conductivity and reliable corrosion protection. Thanks to its excellent flexibility, the braid is easy to install and is ideal for use in machine building, control cabinet construction, and industrial automation.

General Specifications

Cross-section	7.88 mm ²
Put-up	Spool at 100 m

Mechanical Specifications

Material	Electrolytic copper
Structure	36 x 7 x 0,20 mm
Inner-Ø norm.	8.5 mm
Inner-Ø max.	25.0 mm

Approvals

Compliance	CE, RoHS, REACH
------------	-----------------