


## LED PIPE 1500

LED PIPE 1500 520LM 6W L300 4000K

0051019

**Range Features**

- LED T5 batten 800lm/m ideal for cove lighting and secondary illumination
- LED T5 batten 1500lm/m high lumen output ideal for direct lighting such as under cabinet or in kitchens
- LED T5 batten 1500lm includes integrated switch
- Driver integrated, direct input 220-240V
- Seamless linking - up to 10m
- Tilttable mounting bracket included
- High quality robust PC extrusion tube
- Uniform light distribution
- Easy installation by mounting brackets ( 2 non-tiltable + 2 tilttable included)
- Available in approximately 300/600/900/1200mm length
- Available in 3000K and 4000K
- Low maintenance with 30,000 hours LED life expectancy
- LED technology provides energy efficient solution and reduced maintenance cost

**PRODUCT OVERVIEW**

<b>Certifications</b>	CE
<b>Colour temperature (K)</b>	4000
<b>Colour</b>	White
<b>CRI (Ra)</b>	80
<b>EAN code</b>	5410288510194
<b>Luminous flux (lm)</b>	520
<b>Housing</b>	Polycarbonate
<b>IP rating</b>	IP20
<b>Light colour</b>	Cool white
<b>LOR (%)</b>	100
<b>Mount</b>	Surface mounted
<b>Ordering number</b>	0051019
<b>Efficacy (Rated) (lm/w)</b>	87
<b>Average life (Rated) (h)</b>	30000
<b>Technology</b>	LED
<b>Voltage (V)</b>	100-240
<b>Included lamp</b>	Integrated LED

**DATA TABLE**

## General data

<b>Certifications</b>	CE
<b>EAN code</b>	5410288510194
<b>Environment</b>	Internal

## LED PIPE 1500

LED PIPE 1500 520LM 6W L300 4000K

0051019

<b>General application</b>	Residential & Consumer
<b>Housing</b>	Polycarbonate
<b>Mount</b>	Surface mounted
<b>Ordering number</b>	0051019
	LED T5 batten 800lm/m ideal for cove lighting and secondary illumination
	LED T5 batten 1500lm/m high lumen output ideal for direct lighting such as under cabinet or in kitchens
	LED T5 batten 1500lm includes integrated switch
	Driver integrated, direct input 220-240V
	Seamless linking - up to 10m
	Tiltable mounting bracket included
<b>Range features</b>	High quality robust PC extrusion tube
	Uniform light distribution
	Easy installation by mounting brackets ( 2 non-tiltable + 2 tiltable included)
	Available in approximately 300/600/900/1200mm length
	Available in 3000K and 4000K
	Low maintenance with 30,000 hours LED life expectancy
	LED technology provides energy efficient solution and reduced maintenance cost
<b>Product name</b>	LED PIPE 1500 520LM 6W L300 4000K
<b>Average life (Rated) (h)</b>	30000
<b>Technology</b>	LED
<b>Product features</b>	LED Batten T5 1500lm per metre, 520LM, 6W, L300, 4000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 282mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.

## Optical data

<b>Colour temperature (K)</b>	4000
<b>CRI (Ra)</b>	80
<b>Distribution type</b>	Direct
<b>Luminous flux (lm)</b>	520
<b>Light colour</b>	Cool white
<b>LOR (%)</b>	100

## Physical data

<b>Colour</b>	White
<b>Diffuser finish</b>	Frosted
<b>Height (mm)</b>	36
<b>IP rating</b>	IP20
<b>Lamp included</b>	Integrated
<b>Length (mm)</b>	282
<b>Width (mm)</b>	24
<b>Included lamp</b>	Integrated LED

## LED PIPE 1500


LED PIPE 1500 520LM 6W L300 4000K

0051019

### Electrical data


Electrical protection	CLASS 2
Efficacy (Rated) (lm/w)	87
Total power consumption (W)	6
Voltage (V)	100-240

### PHOTOMETRY




Distance [m]	Cone diameter [m]	Beam diameter [m]	Illuminance [lx]
0.5	21.20 1.38	0.7° 0.9° 0.9°	481 0 45
1.0	42.41 2.76	0.7° 0.9° 0.9°	113 0 11
1.5	63.61 4.14	0.7° 0.9° 0.9°	50 0 5
2.0	84.82 5.53	0.7° 0.9° 0.9°	23 0 3
2.5	106.02 6.91	0.7° 0.9° 0.9°	18 0 2
3.0	127.23 8.29	0.7° 0.9° 0.9°	13 0 1

### TECHNICAL DRAWINGS




Power	L1	L2	W	H
4/6W	270mm	262mm	24mm	36mm
7/11W	570mm	562mm	24mm	36mm
10/17W	870mm	862mm	24mm	36mm
14/22W	1170mm	1162mm	24mm	36mm



## LED PIPE 1500


LED PIPE 1500 520LM 6W L300 4000K

**0051019**




This luminaire contains built in LED lamps.

The lamps cannot be changed in the luminaire.



**A++**  
**A+**  
**A**  
~~**B**~~  
~~**C**~~  
~~**D**~~  
~~**E**~~

**LED**



**SYLVANIA** 0051019

874/2012