




zQSFP+/QSFP28

TE Internal #: 2333801-2
QSFP28 Cable Assembly, 16 Positions, 1 m [3.28 ft], 25 Gb/s, Black
Cable, Shielded, 30 AWG, .051 mm² Wire, QSFP28 Plug End A,
QSFP28 Plug End B, CL2

[View on TE.com >](#)

Cable Assemblies > Copper Cable Assemblies > Pluggable I/O Cable Assemblies > QSFP28-Two QSFP28 Cable Assembly: 30 AWG



Cable Assembly Type: **QSFP28**
Number of Positions: **16**
Cable Assembly Length: **1 m [3.28 ft]**
Data Rate: **25 Gb/s**
Cable Color: **Black**

[All QSFP28-Two QSFP28 Cable Assembly: 30 AWG \(6\)](#)

Features

Product Type Features

Latching Style	Slide Latch
Cable Assembly Category	High Speed, Industry Standard
Cable Assembly Type	QSFP28
Cable Style	Madison TurboTwin - Round Jacketed
Cable Assembly (End A)	QSFP28 Plug
Cable Assembly (End B)	QSFP28 Plug

Configuration Features

Number of Positions	16
Number of Pairs	8
Number of Signal Positions	16

Electrical Characteristics

Impedance	100 Ω
-----------	-------



Signal Characteristics

Data Rate	25 Gb/s
-----------	---------

Body Features

Cable Color	Black
Equalized	No
Cable Flammability Rating	CL2

Dimensions

Wire Size	.051 mm²
Outside Cable Diameter	6.2 mm[.244 in]

Operation/Application

Shielded	Yes
Halogen Free	No

Other

Cable Assembly Configuration	Double Ended
Cable Assembly Length	1 m[3.28 ft]

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for



substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # 2170807-3 CAGE ASSY, 1X2, QSFP28, SPRING, QUAD LP	 TE Part # 2314014-1 STRADDLE MOUNT QSFP28, 1X6, RECEPTACLE	 TE Part # 2314015-1 STRADDLE MOUNT QSFP28, 1X6, RECEPTACLE	 TE Part # 5-2170703-2 CAGE ASSEMBLY, QSFP28 1X1, SPRING
 TE Part # 6-2170705-1 CAGE ASSY, QSFP28 1X1, SPRING, HS, LP	 TE Part # 2170739-3 QSFP28, 1X3, CAGE ASSY, SPRING, LP	 TE Part # 2274085-1 Cage Assy 1x1 Behind Bezel Gasket QSFP28	 TE Part # 1-2170704-2 CAGE ASSY, QSFP28 1X1, SPRING, HS
 TE Part # 2320645-1 CAGE ASSEMBLY, 1X2, QSFP28, SPRING,HS,8LP	 TE Part # 4-2170814-3 QSFP28, 1X2, CAGE ASSY, GASKET, HS, LP	 TE Part # 2170812-4 CAGE ASSEMBLY, 1X2, QSFP28, GASKET, HS	 TE Part # 1-2170740-2 QSFP28, 1X3, CAGE ASSY, SPRING, HS
 TE Part # 5-2289708-1 QSFP28, 1X3, CAGE ASSY, SPRING, HS, SQLP	 TE Part # 2170811-5 CAGE ASSEMBLY, 1X2, QSFP28, GASKET	 TE Part # 2-2170814-3 QSFP28, 1X2, CAGE ASSY, GASKET, HS, LP	 TE Part # 2170812-2 CAGE ASSEMBLY, 1X2, QSFP28, GASKET, HS



TE Part # 2306002-1
STRADDLE MOUNT QSFP28, 1X2, RECEPTACLE

TE Part # 2170790-6
CAGE ASSY, 1X4, QSFP28, SPRING, HS

TE Part # 2-2170754-5
CAGE ASSY, QSFP28 1X1, GASKET, HS, LP

TE Part # 2-2170814-6
QSFP28, 1X2, CAGE ASSY, GASKET, HS, LP

Also in the Series | [zQSFP+/QSFP28](#)

Pluggable I/O Cable Assemblies(78)

Pluggable IO Connectors & Cages(424)

QSFP, QSFP+ & zQSFP+(424)

Customers Also Bought

TE Part #2-1445054-2
MICRO MNL HDR ASSY S/ROW LF

TE Part #3-794680-4
04P MICRO MNL ASSY,VRT,THRU LF

TE Part #4-794677-2
12POS MICRO MNL ASSY,R/A,THRU

TE Part #1-1456426-5
4POS, MCON 1.2 CB REC 2p TL SEALED

TE Part #1445022-2
MICRO MNL RECEPT HSG SINGLE R

TE Part #2-1445051-2
MICRO MNL HDR ASSY S/ROW LF

TE Part #3-794680-6
06P MICRO MNL ASSY,VRT,THRU LF

TE Part #4-1904065-7
V23720A0002A001-EV-CBOX

TE Part #1-1393236-3
V23092A1012A801

TE Part #4-794677-8
18POS MICRO MNL ASSY,R/A,THRU



Documents

Product Drawings

QSFP TO (2)QSFP, 25G, 1 METER, 30AWG

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2333801-2_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2333801-2_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2333801-2_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Product Specification

English

Connector, CHAMP

English

Connector, CHAMP

Japanese

Product Specification

Japanese