

**Rexel Shredder Oil**

ACCORDING TO EC-REGULATIONS 1907/2006 (REACH), 1272/2008 (CLP) & 2020/878

SECTION 1: IDENTIFICATION OF THE SUBSTANCE/MIXTURE AND OF THE COMPANY/UNDERTAKING**1.1 Product identifier**

Product Name	Rexel Shredder Oil
Chemical Name	White mineral oil (petroleum)
Product code	Oil Bottle: 1760049 Shredder with sample oil bottle: 2102421EU, 2102425EU, 2102429EU, 2102437EU, 2102565EU, 2102566EU, 2103500EU, 2104500EU, 2102446, 2102449, 2103039EU, 2103750EU, 2102443, 2102421,
CAS No.	8042-47-5
EC No.	232-455-8
REACH Registration No.	01-2119487078-27-XXXX

1.2 Relevant identified uses of the substance or mixture and uses advised against

Identified Use(s)	Consumer use, Professional use – Shredder Lubricant.
Uses Advised Against	Not known.

1.3 Details of the supplier of the safety data sheet

Manufacturer	
Company Identification	Acco UK Ltd. Millennium House, 65 Walton Street. Aylesbury. Bucks. HP21 7QG
Telephone	+44 (0) 844 209 8360
Fax	+44 (0) 845 603 1731
E-mail	informationeurope@acco.com
Website	www.acco.co.uk
Office hours	09:00 - 17:00
Supplier	
Company Identification	Esselte SAS 9 avenue Edouard Belin 92500 Rueil-Malmaison Cedex France
Telephone	+33 (01) 49 68 13 00
E-mail	contactfrance@acco.com
Website	www.esselte.com
Office hours	09:00 - 17:00

1.4 Emergency telephone number

Company (United Kingdom)	+44 (0) 844 209 8360 (09:00 - 17:00)
Company (France)	+33 (01) 49 68 13 00 (09:00 - 17:00)

SECTION 2: HAZARDS IDENTIFICATION**2.1 Classification of the substance or mixture**

Regulation (EC) No. 1272/2008 (CLP) Not classified as dangerous for supply/use.

2.2 Label elements

	According to Regulation (EC) No. 1272/2008 (CLP)
Product Name	Rexel Shredder Oil

**Rexel Shredder Oil**

Hazard Pictogram(s) None.
Signal Word(s) None.
Hazard Statement(s) None.
Precautionary Statement(s) None.

2.3 Other hazards

None known.

2.4 Additional Information

None.

SECTION 3: COMPOSITION/INFORMATION ON INGREDIENTS**3.1 Substances**

HAZARDOUS INGREDIENT(S)	CAS No.	EC No. / REACH Registration No.	%W/W	Hazard Statement(s)	Hazard Pictogram(s)
White mineral oil (petroleum)	8042-47-5	232-455-8 01-2119487078-27-XXXX	>99	Not classified	None

Contains no non-classified vPvB substances.

Contains no non-classified substances with a Union workplace exposure limit.

3.2 Mixtures

Not applicable.

SECTION 4: FIRST AID MEASURES**4.1 Description of first aid measures**

Inhalation If breathing is difficult, remove victim to fresh air and keep at rest in a position comfortable for breathing.

Skin Contact Wash skin with soap and water. If symptoms persist, obtain medical attention.

Eye Contact Flush eyes with water for at least 15 minutes. If symptoms develop, obtain medical attention.

Ingestion Wash out mouth with water. If symptoms persist, obtain medical attention.

4.2 Most important symptoms and effects, both acute and delayed

None anticipated.

4.3 Indication of any immediate medical attention and special treatment needed

Unlikely to be required but if necessary treat symptomatically.

SECTION 5: FIREFIGHTING MEASURES**5.1 Extinguishing media**

Suitable Extinguishing media Extinguish preferably with dry chemical, foam, waterspray or sand.

Unsuitable extinguishing media Do not use water jet.

5.2 Special hazards arising from the substance or mixture

May decompose in a fire giving off toxic fumes.

5.3 Advice for firefighters

A self contained breathing apparatus and suitable protective clothing should be worn in fire conditions.

Rexel Shredder Oil

SECTION 6: ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

General hygiene measures for the handling of chemicals are applicable. Avoid inhalation of high concentrations of vapours.

6.2 Environmental precautions

Do not allow to enter drains, sewers or watercourses.

6.3 Methods and material for containment and cleaning up

Soak up with inert absorbent. Transfer to a container for disposal.

6.4 Reference to other sections

See Also Section 8, 13.

SECTION 7: HANDLING AND STORAGE

7.1 Precautions for safe handling

Provide adequate ventilation when using the material and follow the principles of good occupational hygiene to control personal exposures. Avoid inhalation of high concentrations of vapours. Do not eat, drink or smoke at the work place. Wash hands thoroughly after handling.

7.2 Conditions for safe storage, including any incompatibilities

Keep container tightly closed.

Storage temperature

Ambient.

Storage life

Stable under normal conditions.

Incompatible materials

None known.

7.3 Specific end use(s)

Consumer use, Professional use – Shredder Lubricant.

SECTION 8: EXPOSURE CONTROLS/PERSONAL PROTECTION

8.1 Control parameters

8.1.1 Occupational Exposure Limits

SUBSTANCE	CAS No.	LTEL (8 hr TWA ppm)	LTEL (8 hr TWA mg/m ³)	STEL (ppm)	STEL (mg/m ³)	Note
						None assigned

Source: UK Workplace Exposure Limits EH40/2005 (Fourth edition, published 2020)

8.2 Exposure controls

8.2.1. Appropriate engineering controls Ensure adequate ventilation.

8.2.2. Personal protection equipment



Eye Protection

Not normally required.



Skin protection

Wear suitable gloves if prolonged skin contact is likely.

Breakthrough time of the glove material: refer to the information provided by the gloves' producer.

Rexel Shredder Oil



Respiratory protection Normally no personal respiratory protection is necessary.



Thermal hazards Not applicable.

8.2.3. Environmental Exposure Controls Do not allow to enter drains, sewers or watercourses.

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Physical state	Liquid.
Colour	Colourless.
Odour	Odourless.
Melting point/freezing point	Not known.
Boiling point or initial boiling point and boiling range	Not known.
Flammability	Non-flammable.
Lower and upper explosion limit	Not known.
Flash Point	186 ° C
Auto-ignition temperature	Not known.
Decomposition Temperature	Not known.
pH	Not known.
Kinematic Viscosity	58.6 mm ² /s @ 40° C
Solubility	Solubility (Water) : Immiscible with water. Solubility (Other) : Not known.
Partition coefficient n-octanol/water (log value)	Not known.
Vapour pressure	Not known.
Density and/or relative density	Density (g/ml): 875 kg/m ³
Relative vapour density	Not known.
Particle characteristics	Not applicable.

9.2 Other information

None.

SECTION 10: STABILITY AND REACTIVITY

10.1 Reactivity

Stable under normal conditions.

10.2 Chemical Stability

Stable under normal conditions.

10.3 Possibility of hazardous reactions

No hazardous reactions known if used for its intended purpose.

10.4 Conditions to avoid

Heat and direct sunlight.

10.5 Incompatible materials

Not known.

Rexel Shredder Oil

10.6 Hazardous decomposition products

No hazardous decomposition products known.

SECTION 11: TOXICOLOGICAL INFORMATION

11.1 Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity - Ingestion	Low oral toxicity. LD50 (oral) mg/kg: >5000 (rat)
Acute toxicity - Skin Contact	Low acute toxicity. LD50 (dermal) mg/kg: >2000 (rabbit)
Acute toxicity - Inhalation	Low acute toxicity. LC50 (inhalation) mg/l/4h: >5 (rat) (Aerosol)
Skin corrosion/irritation	Non-irritant.
Serious eye damage/irritation	Not classified.
Skin sensitization data	It is not a skin sensitizer.
Respiratory sensitization data	Not classified.
Germ cell mutagenicity	There is no evidence of mutagenic potential.
Carcinogenicity	No evidence of carcinogenic effects.
Reproductive toxicity	No evidence of reproductive effects.
Lactation	Not classified.
STOT - single exposure	None anticipated.
STOT - repeated exposure	None anticipated.
Aspiration hazard	Not classified.

11.2 Information on other hazards

Not known.

SECTION 12: ECOLOGICAL INFORMATION

12.1 Toxicity

Toxicity - Aquatic invertebrates	Low toxicity to invertebrates.
Toxicity - Fish	Low toxicity to fish. LC50 (golden orfe (Leuciscus idus)) mg/l: > 10000 (96 hour) LC50 (rainbow trout) mg/l: >100 (96 hour)
Toxicity - Algae	Low toxicity to algae.
Toxicity - Sediment Compartment	Not classified.
Toxicity - Terrestrial Compartment	Not classified.

12.2 Persistence and degradability

No information available.

12.3 Bioaccumulative potential

No information available.

12.4 Mobility in soil

Insoluble in water. The product is predicted to have low mobility in soil.

12.5 Results of PBT and vPvB assessment

Not classified as PBT or vPvB.

12.6 Endocrine disrupting properties

None known.

12.7 Other adverse effects

Not known.

Rexel Shredder Oil

SECTION 13: DISPOSAL CONSIDERATIONS

13.1 Waste treatment methods

Dispose at suitable refuse site.

13.2 Additional Information

Dispose of contents in accordance with local, state or national legislation.

SECTION 14: TRANSPORT INFORMATION

Not classified as hazardous for transport.

14.1 UN number or ID number

Not applicable

14.2 UN proper shipping name

Not applicable

14.3 Transport hazard class(es)

Not applicable

14.4 Packing group

Not applicable

14.5 Environmental hazards

Not classified as a Marine Pollutant.

14.6 Special precautions for user

Not known

14.7 Maritime transport in bulk according to IMO instruments

Not known

SECTION 15: REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

European Regulations - Authorisations and/or Restrictions On Use

Candidate List of Substances of Very High Concern for Authorisation

Not listed

REACH: ANNEX XIV list of substances subject to authorisation

REACH: Annex XVII Restrictions on the manufacture, placing on the market and use of certain dangerous substances, mixtures and articles

Not listed

Community Rolling Action Plan (CoRAP)

Not listed

Regulation (EU) N° 2019/1021 of the European Parliament and of the Council on persistent organic pollutants

Not listed

Regulation (EC) N° 1005/2009 on substances that deplete the ozone layer

Not listed

Regulation (EU) N° 649/2012 of the European Parliament and of the Council concerning the export and import of

Not listed

Not listed

Not listed

Not listed

**Rexel Shredder Oil**

hazardous chemicals

National regulations

Other

Not known.

15.2 Chemical Safety Assessment

A REACH chemical safety assessment has not been carried out.

SECTION 16: OTHER INFORMATION

The following sections contain revisions or new statements: 1-16

LEGEND

Company Identification:

Address change

Acronyms

CAS : Chemical Abstracts Service

CLP : Regulation (EC) No 1272/2008 on classification, labelling and packaging of substances and mixtures

EC : European Community

LTEL : Long term exposure limit

PBT : Persistent, Bioaccumulative and Toxic

REACH : Registration, Evaluation, Authorisation and Restriction of Chemicals

STEL : Short term exposure limit

STOT : Specific Target Organ Toxicity

vPvB : very Persistent and very Bioaccumulative

Key literature references and sources
for data used to compile the SDS

Regulation (EC) No. 1272/2008 (CLP)

Disclaimers

Information contained in this publication or as otherwise supplied to Users is believed to be accurate and is given in good faith, but it is for the Users to satisfy themselves of the suitability of the product for their own particular purpose. Acco UK Ltd. gives no warranty as to the fitness of the product for any particular purpose and any implied warranty or condition (statutory or otherwise) is excluded except to the extent that exclusion is prevented by law. Acco UK Ltd. accepts no liability for loss or damage (other than that arising from death or personal injury caused by defective product, if proved), resulting from reliance on this information. Freedom under Patents, Copyright and Designs cannot be assumed.