

Parker Product Datasheet



The replacement elements of the Parker BGT Filter Series feature high quality filter materials. Leif elements with reusable metal sleeve are patented and safeguard the use of genuine parts.

PART NUMBER: 937773Q
LENGTH: 825 mm
SEAL MATERIAL: Nitrile
DIAMETER: 203 mm
FILTER ELEMENT TYPE: 10Q Microglass with inner core
MICRON RATING: 10 μ m
FILTER HOUSING SERIES: BGT16 (4-1500)

PRODUCT OVERVIEW

The high quality replacement elements of the BGT filter series are available in a wide variety of sizes and with several filter materials and micron ratings.

These replacement elements ensure the quality of filtration Parker is known for.

Fluid passes through the elements in an inside-to-outside direction, collecting particles inside the filter cartridge. This eliminates reinjection of contaminant during element change. Clean fluid then returns to the reservoir.

The BGT series filters are available with Magnetic pre-filtration. The magnet column removes ferrous particles, even during times of bypass, and extends the life of the filter element.

Using genuine Parker replacement elements guarantees Parker's quality of filtration. Using after market filters with unknown media quality may save initial cost, but can increase overall costs by

requiring more element change outs and potentially causing system downtime. Protect your investment by always buying genuine Parker replacement elements.

TECH SPECIFICATIONS

DIVISION	Hydraulic & Industrial Process Filtration Division EMEA
DIVISION	Hydraulic & Industrial Process Filtration Division EMEA
BRAND	Parker
TECHNOLOGY	Filtration
TECHNOLOGY	Hydraulics
PRODUCT STYLE	Conventional disposable element
PRODUCT TYPE	Hydraulic Filter Replacement Part
MAXIMUM PRESSURE DIFFERENTIAL	10 bar (ISO 2941)