


Retro-reflective sensor

OGP-HPKG/US/90°



Product characteristics

Type of light	red light
Housing	threaded type

Application

Special feature	polarisation filter
Function principle	Retro-reflective sensor

Electrical data

Operating voltage	[V]	10...30 DC; ("supply class 2" to cULus)
Current consumption	[mA]	< 22
Protection class		II
Reverse polarity protection		yes
Type of light		red light
Wave length	[nm]	660

Outputs

Electrical design		PNP
Output function		light-on mode
Max. voltage drop switching output DC	[V]	2.5
Permanent current rating of switching output DC	[mA]	200
Switching frequency DC	[Hz]	500
Short-circuit protection		yes
Type of short-circuit protection		pulsed
Overload protection		yes

Detection zone

Range referred to prismatic reflector	[m]	3; (Prismatic reflector Ø 80 E20005)
Range adjustable		no



Retro-reflective sensor

OGP-HPKG/US/90°

Max. light spot diameter	[mm]	96
Light spot dimensions refer to		at maximum range
Polarisation filter available		yes

Operating conditions

Ambient temperature	[°C]	-25...60
Protection		IP 68

Tests / approvals

EMC	EN 60947-5-2	
	EN 55011	class B
MTTF	[years]	859

Mechanical data

Weight	[g]	59.5
Housing		threaded type
Dimensions	[mm]	M18 x 1 / L = 59.3
Thread designation		M18 x 1
Materials		stainless steel; ABS
Lens material		PMMA

Displays / operating elements

Display	switching status	1 x LED, yellow
	operation	1 x LED, green

Accessories

Items supplied	Nuts: 2
	lock washers: 2

Remarks

Pack quantity	1 pcs.
---------------	--------

Electrical connection

Connector: 1 x M12; coding: A





Retro-reflective sensor

OGP-HPKG/US/90°

Connection

