

40Vmax Pruning Saw Brushless XGT®

UC029G

150 mm, 8,0 m/s

Model UC029G is a 150mm pruning saw powered by 40V XGT Li-Ion battery

Maintaining a light weight and compact body, the motor with the increased size allows for smoother cutting of shrubs and small branches. The main features and benefits are: Tool-less change and tension adjustment of saw chain. Equipped with a rear hand guard. Moveable guard. Saw chain: 80TXL.



Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Max. Chain Speed (No Load)	8,0 m/s
chain bar length	150 mm (6")
Chain Pitch	0,325 "
Chain Gauge	0,043 "
Chain Gauge	1,1 mm
Number of Drive Links	32
Chain Oil Tank	55 ml
Brushless Motor	✓
Vibration Level, Cutting Wood	4,6 m/s ²
Vibration Uncertainty (K Factor), Cutting Wood	1,5 m/s ²
Sound Pressure Level (L _{pA})	81 dB(A)
Sound Power Level (L _{WA})	89 dB(A)

User benefits

- Automatic chain lubrication
- eXtreme Protection Technology (XPT) is engineered for improved dust and water resistance for operation in harsh conditions
- Electric brake for maximum productivity and increased operator safety

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing