



## Relamp LED T8 Tube Batten 1200 G13 1x36W IP65 IK10

Article number: 146961

BAL Surface-mounted Batten for LED Tube T8 1200mm G13 230V/AC (lamp not included) Max. 36W LED IP65 IK10 CLI 1260x70x68mm

Waterproof fixtures with replaceable bulbs are more sustainable than fixtures with a fixed LED element. Replacing energy-efficient light sources when they reach the end of their lifespan is simply more sustainable than replacing the entire fixture. That's why Bailey Lights offers Relamp fixtures. This IP65 IK10 fixture (also called batten or tri-proof) houses a T8 220-240Vac LED tube with a G13 base. The waterproof fixture is suitable for one LED tube, has no ballast, and is easy to mount to the ceiling and connect. This fixture is supplied without an LED tube; you can choose the LED tube that best suits your situation. Bailey offers a wide selection. Accessories are included (two PG13.5 cable glands, Stainless steel locking clips, and mounting clips). Note: This fixture is only suitable for LED tubes. Ideal for damp areas, garages, porches, and galleries.

### General ETIM properties

ETIM group	Luminaires
ETIM class	Ceiling-/wall luminaire
Name	Relamp LED T8 Tube Batten 1200 G13 1x36W IP65 IK10
Brand	Bailey
Productseries	BaiLum surface-mounted
Producttype	LED Tube T8 Batten

## ETIM specifications

Lamp holder	G13
Housing colour	Grey
With movement sensor	No
With light sensor	No
Width [mm]	70
Length [mm]	1260
Nominal voltage [V]	220 - 240
Impact strength	IK10
Dimmable	No
Suitable for suspended mounting	No
Suitable for ceiling mounting	Yes
Suitable for built-in mounting	No
Suitable for surface mounting	No
Suitable for light line configuration	No
Suitable for workplace according to EN 12464-1	Yes
Lamp type	LED not exchangeable
With light source	No
Suitable for emergency lighting	No
Suitable for number of light sources	1
Housing material	Plastic
Material cover	Plastic, transparent
Type of grid	None
Voltage type	AC
With control gear	No
Exchangeable control gear	No
Dimming 0-10 V	No
Dimming 1-10 V	No
Dimming DALI-2	No
Dimming DALI	No
Dimming DMX	No
Dimming DSI	No
Dimming potentiometer (integrated)	No
Dimming manufacturer's proprietary system	No
Dimming mains voltage modulation	No
Dimming phase cut-off (trailing edge)	No
Dimming phase cut-on (leading edge)	No
Dimming programmable	No
Dimming RF	No
Dimming Touch and Dim	No
Dimming Zigbee	No
Dimming with push-button	No

Light distributor	None
Beam angle	> 80° - Extreme wide beam
Max. number of luminaires per miniature circuit breaker B16 (MCB)	300
Degree of protection (NEMA)	Other
Protection class according to IEC 61140	I
Luminaire with limited surface temperature, sign "D" according to EN 60598-2-24	Yes
Rated ambient temperature according to IEC 62722-2-1 [°C]	-20 - 40
Covering of the luminaire with thermally insulating material possible	No
With air slots	No
Filament test according to IEC 60695-2-11	None
Suitable for lamp power [W]	36 - 36
Max. system power [W]	300
Height/depth [mm]	68
Type of wiring	Suitable for loop-through wiring
Number of poles	3
Conductor cross section [mm²]	0.75
Connection type	Screwed terminal
Colour of light adjustable	No
Luminous flux adjustable	No
Beam angle adjustable	No
Operation by Bluetooth	No
Compatible with Apple HomeKit	No
Compatible with Google Assistant	No
Compatible with Amazon Alexa	No
IFTTT support available	No
Suitable for wall mounting	Yes
Compatible with Casambi	No
Meets min. EIA lifetime criterion L90 (at 50,000 hours at tq = 25 °C)	No
Suitable for clamp-mounting	No
With mounting material	Yes
Containing product according to 2019/2020/EU	No
Degree of protection (IP), rear side	Other
Degree of protection (IP), front side	IP65
Emergency power supply system	None
Emergency function monitoring system	None
With switch	No
With presence detector	No
Connectable conductor cross section [mm²]	0.5 - 2.5
Ball-proof according to DIN 18032-3	No

## Complementary articles



80100040813

LED Ecobasic T8 1200 G13 20W  
(36W) 2100lm 830 EM+AC



80100040814

LED Ecobasic T8 1200 G13 20W  
(36W) 2200lm 840 EM+AC