


FEATURES

- They are suitable for measurement of both static and dynamic applications
- Wide temperature range
- Clear alignment marks
- Can be affixed with epoxy
- Each strain gauge has been fitted with leads

RS PRO Wire Lead Strain Gauge 2.5mm, 120 Ω -30°C +80°C

RS Stock No.: 632-124



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Our RS PRO strain gauges have been created and designed to measure the strain and force of an item, each foil strain gauge has a laminated surface with 30 mm integral leads. The gauge sticks to an item, as it deforms the electrical resistance changes - this process can sometimes be referred to as the "gauge factor". Our RS Pro strain gauges can be used in a multitude of applications for strain measurement, such as keypads, medical devices and automotive products.

General Specifications

Gauge Factor	2
Gauge Resistance	120Ω
Terminal Type	Wire Lead
Fatigue Life	>10 ⁶ reversals at 1000μ strain

Mechanical Specifications

Dimensions	6mm x 2.5mm
Gauge Length	2mm
Length	6mm
Width	2.5mm

Operation Environment Specifications

Minimum Operating Temperature	-30°C
Maximum Operating Temperature	+80°C

Approvals

Compliance/Certifications	CE
---------------------------	----