



TE Internal #: 1565322-1
Preloaded - C-Clip PCB Spring Contact, 1.6 mm [.063 in]
Uncompressed Height, 3.2 mm [.126 in] Length, .75 mm [.03 in]
Width
[View on TE.com >](#)

Connectors > Contacts > PCB Spring Contacts



Spring Finger Type: **Preloaded - C-Clip**
Scalable: **No**
Side Protected: **No**
Uncompressed Height: **1.6 mm [.063 in]**
Product Length: **3.2 mm [.126 in]**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Connector System	Board-to-Board
Spring Finger Type	Preloaded - C-Clip
Scalable	No

Configuration Features

Number of Positions	1
Side Protected	No

Contact Features

Contact Underplating Material	Nickel
Contact Base Material	Copper Alloy
PCB Contact Termination Area Plating Material	Gold
Contact Working Range (Low)	1 mm[.039 in]
Contact Working Range (High)	1.3 mm[.051 in]
Point of Contact Area Plating Material	Gold



Contact Current Rating (Max)	1.5 A
------------------------------	-------

Dimensions

Uncompressed Height	1.6 mm[.063 in]
Product Length	3.2 mm[.126 in]
Product Width	.75 mm[.03 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Method	Tape & Reel
Packaging Quantity	5000

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2023 (235) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2305018-2
USB TYPE C, REC IPX8 ON BOARD
DUAL SMT

Customers Also Bought




TE Part #41532
250 FASTON FLAG REC 18-12 AWG
TPBR



TE Part #2-1462039-6
IM21GR=IM RELAY 50mW 3V



TE Part #6-1676915-8
YR1 0.1% 124R



TE Part #640457-9
09P MTA100 HDR ASSY SQ R/A F/L




TE Part #1SNA179668R2000
BJMI6D-2



TE Part #1622442-1
LR1 1% 33R




TE Part #5-1879377-8
CRGH0805 5% 220R 0.33W



TE Part #2176082-5
EP 3W (S) 47R 5%



TE Part #223956-1
STV ERMZUB FUEHRUNGSBOLZEN J
* M 1 ***



TE Part #6-103634-3
14 MTE HDR SRRA LTCH.100CL LF

Documents

Product Drawings
SHIELD FINGER 1608

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_1565322-1_D1.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1565322-1_D1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1565322-1_D1.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Products for Mobile Equipment](#)

English

Product Specifications

[Shield Finger 1608](#)

Japanese

[Product Specification](#)

Japanese