

FAG


21318-E1-XL

Spherical Roller Bearing

Spherical roller bearings 213...-E1, main dimensions to DIN 635-2

X-life

Technical information



Your current product variant

Design	E1	without central rip
Bore type	Z	Cylindrical
Cage	JPA	Sheet metal cage
Radial internal clearance	CN (Group N)	Normal internal clearance
Relubrication feature	Standard	

Main Dimensions & Performance Data

d	90 mm	Bore diameter
D	190 mm	Outside diameter
B	43 mm	Width
C _r	380,000 N	Basic dynamic load rating, radial
C _{0r}	415,000 N	Basic static load rating, radial
C _{ur}	48,500 N	Fatigue load limit, radial
n _G	4,850 1/min	Limiting speed
n _{gr}	3,600 1/min	Reference speed
≈m	6.124 kg	Weight



Mounting dimensions

d _{a min}	104 mm	Minimum diameter shaft shoulder
D _{a max}	176 mm	Maximum diameter of housing shoulder
r _{a max}	2.5 mm	Maximum recess radius

Dimensions

r _{min}	3 mm	Minimum chamfer dimension
D ₁	152.7 mm	Bore diameter outer ring
d ₂	112.6 mm	Raceway diameter of the inner ring
d _s	4.8 mm	Diameter lubrication hole
n _s	9.5 mm	Width of lubricating groove

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	200 °C	Operating temperature max.

Calculation factors

e	0.24	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y ₁	2.87	Dynamic axial load factor
Y ₂	4.27	Dynamic axial load factor
Y ₀	2.8	Static axial load factor



Characteristics

-  Radial load
-  Axial load in one direction
-  Axial load in two directions
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed
-  Static angular error and misalignment
-  Dynamic angular error and misalignment