

Product data sheet

Specifications



Repacked Workstation, New Unica, flush, 3 x 4 modules vertical, white

NU173418W



This repacked option saves 3.12 over the standard condition

Main

Range	New Unica
Product or component type	Workstation
Number of modules	3 x 4 modules
Mounting position	Vertical
fixing mode	Embedment Claws

Complementary

Provided equipment	Fixing frame Cover frame
Device mounting	Flush
Cable entry	6 knock-outs 20 mm for diameter 6 knock-outs 25 mm for diameter 2 bottom cable entries 45 x 25 mm for size 20 mm for diameter 4 bottom cable entries 50 x 35 mm for size 25 mm for diameter
Fire resistance	850 °C, extinction time <30 s
Material	ABS (acrylonitrile butadiene-styrene): separator PC: box ABS (acrylonitrile butadiene-styrene): cover frame
Depth	62 mm
Width	230 mm
Height	165 mm
Product weight	0.401 kg
resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK04
-------------------------	------

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 1 Height	7.9 cm
Package 1 Width	17.9 cm
Package 1 Length	25.0 cm
Package 1 Weight	520.0 g
Unit Type of Package 2	S04
Number of Units in Package 2	14
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	7.794 kg
Unit Type of Package 3	P06
Number of Units in Package 3	56
Package 3 Height	77.0 cm
Package 3 Width	80.0 cm
Package 3 Length	60.0 cm
Package 3 Weight	40.66 kg

Contractual warranty

Warranty (in months)	18
----------------------	----

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint	
Lower carbon footprint	3 kg CO2 eq.

Use Better

Materials and Substances	
SCIP Number	Ce89f989-36a8-4890-9b3e-79150ca1abc2
EU RoHS Directive	Compliant
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer

Lifetime extension	
Repair	No

Use Again

Repack and remanufacture	
Take-back	No
WEEE Label	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins