


STANDARD BUMPING

PART NO.	SIZE Wgt (g)	Overall L (mm)	A (mm)	B (mm)	L (mm)			G.W. (kg)
92101	320	330	41	38	97	6	36	16.4


- Flat faces, Polish striking heads & cheeks



HEAVY SHRINKING

PART NO.	SIZE Wgt (g)	Overall L (mm)	A (mm)	B (mm)	L (mm)			G.W. (kg)
92102	390	330	48	41	97	6	36	15.6


- Flat faces, milled square face, Polish striking heads & cheeks



CURVED PEIN & FINISHING

PART NO.	SIZE Wgt (g)	Overall L (mm)	A (mm)	B (mm)	L (mm)			G.W. (kg)
92103	305	330	41	—	140	6	36	16.6

- Flat faces, Polish striking heads & cheeks




LIGHT SHRINKING

PART NO.	SIZE Wgt (g)	Overall L (mm)	A (mm)	B (mm)	L (mm)			G.W. (kg)
92104	320	330	41	38	97	6	36	15.2

- Flat faces, Milled square face, Polish striking heads & cheeks

ASME B107.56-1999




STRAIGHT PEIN & FINISHING

PART NO.	SIZE Wgt (g)	Overall L (mm)	A (mm)	B (mm)	L (mm)			G.W. (kg)
92105	305	330	41	—	140	6	36	16.2

- Cross faces, Polish striking heads, Pick head & cheeks

ASME B107.56-1999




PICK & FINISHING

PART NO.	SIZE Wgt (g)	Overall L (mm)	A (mm)	B (mm)	L (mm)			G.W. (kg)
92106	260	330	38	—	137	6	36	15.6


- Cross face, with round point pick head to remove low spots when metal finishing
- Polished striking head, pick head & cheeks

ASME B107.56-1999



BALL PEIN - FIBER GLASS

PART NO.	SIZE Wgt (g)	Overall L (mm)			G.W. (kg)
92302	454 / 16oz	335	2	28	10.7
92303	680 / 24oz	390	2	20	5.1
92304	910 / 32oz	390	2	20	5.8



CLAW - FIBER GLASS

PART NO.	SIZE Wgt (g)	Overall L (mm)			G.W. (kg)
92306	454 / 16oz	330	2	20	3.9
92307	680 / 24oz	390	2	20	4.9

