



# XB7NJ07M1

ILLUM. P.B - LED - Latch -1NO - Clear - 230v



[Download your XB7NJ07M1 datasheet](#)



[Characteristics](#) | [Documents & Downloads](#)

## Main

Hide

<b>Range of product</b>	Harmony XB7
<b>Product or component type</b>	Monolithic pushbutton
<b>Device short name</b>	XB7
<b>Mounting diameter</b>	22 mm
<b>Sale per indivisible quantity</b>	10
<b>IP degree of protection</b>	IP20 (rear face) conforming to IEC 60529 IP65 (front face) conforming to IEC 60529
<b>Shape of signaling unit head</b>	Round
<b>Type of operator</b>	Push and push-to-release
<b>Operator profile</b>	Clear unmarked
<b>Contacts type and composition</b>	1 NO
<b>Connections - terminals</b>	Screw clamp terminals: $\leq 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN/IEC 60947-1 Screw clamp terminals: $1 \times 0.34 \dots 2 \times 2.5 \text{ mm}^2$ without cable end conforming to EN/IEC 60947-1
<b>Light source</b>	LED
<b>Bulb base</b>	Integral LED
<b>[Us] rated supply voltage</b>	230 V AC, 50/60 Hz

## Complementary

Hide

<b>CAD overall width</b>	29 mm
<b>CAD overall height</b>	29 mm
<b>CAD overall depth</b>	57.5 mm
<b>Terminals description ISO n°1</b>	(13-14)NO
<b>Product weight</b>	0.023 kg
<b>Device mounting</b>	Fixing hole: $\varnothing 22.5 \text{ mm}$ ( $22.3 +0.4/0$ ) conforming to EN/IEC 60947-1
<b>Fixing center</b>	$\geq 30 \times 40 \text{ mm}$ on support panel, metal, thickness: 1...6 mm $\geq 30 \times 40 \text{ mm}$ on support panel, plastic, thickness: 2...6 mm
<b>Fixing mode</b>	Fixing nut beneath head recommended torque: 2.2 N.m (+/- 0.2 N.m)
<b>Contacts operation</b>	Slow-break
<b>Positive opening</b>	With (only NO) positive opening
<b>Mechanical durability</b>	300000 cycles
<b>Tightening torque</b>	0.8...1.2 N.m conforming to EN 60947-1
<b>Shape of screw head</b>	Cross head compatible with JIS No 1 screwdriver Cross head compatible with Philips no 1 screwdriver Cross head compatible with pozidriv No 1 screwdriver Slotted head compatible with flat $\varnothing 4 \text{ mm}$ screwdriver Slotted head compatible with flat $\varnothing 5.5 \text{ mm}$ screwdriver
<b>Short circuit protection</b>	4 A cartridge fuse type gG conforming to EN/IEC 60947-5-1

<b>[Ui] rated insulation voltage</b>	250 V (degree of pollution: 3) conforming to EN/IEC 60947-1
<b>[Uimp] rated impulse withstand voltage</b>	4 kV conforming to EN/IEC 60947-1
<b>[Ie] rated operational current</b>	0.1 A at 250 V, DC-13, R300 conforming to EN/IEC 60947-5-1 0.22 A at 125 V, DC-13, R300 conforming to EN/IEC 60947-5-1 0.3 A at 240 V, AC-14, D300 conforming to EN/IEC 60947-5-1 0.6 A at 120 V, AC-14, D300 conforming to EN/IEC 60947-5-1
<b>Electrical reliability IEC 60947-5-4</b>	$\Lambda \leq 10\exp(-6)$ at 17 V, 5 mA conforming to EN/IEC 60947-5-4
<b>Signalling type</b>	Steady
<b>Supply voltage limits</b>	195...264 V AC
<b>Current consumption</b>	22...27 mA
<b>Service life</b>	70000 h at rated voltage and 25 °C

## Environment

 Hide

<b>Protective treatment</b>	TH
<b>Ambient air temperature for storage</b>	-40...70 °C
<b>Ambient air temperature for operation</b>	-25...70 °C
<b>Class of protection against electric shock</b>	Class II conforming to IEC 61140
<b>NEMA degree of protection</b>	NEMA 12 conforming to UL 50 E
<b>Standards</b>	EN/IEC 60947-1 EN/IEC 60947-5-1 JIS C 4520 UL 508 CSA C22.2 No 14
<b>Product certifications</b>	CCC GOST
<b>Vibration resistance</b>	5 gn (f = 2...500 Hz) conforming to IEC 60068-2-6
<b>Shock resistance</b>	50 gn (duration = 11 ms) for half sine wave acceleration conforming to IEC 60068-2-27 30 gn (duration = 18 ms) for half sine wave acceleration
<b>Electromagnetic emission</b>	Class B conforming to EN 55011

## Offer Sustainability

 Hide

<b>Sustainable offer status</b>	Not Green Premium product
<b>RoHS (date code: YYWW)</b>	Will not be Compliant

## Contractual warranty

 Hide

<b>Period</b>	18 months
---------------	-----------