

# FLUKE®

# Fluke 115 Multimeter

## Technical Data



### Compact true-rms meter for field service technicians

The Fluke 115 is the solution for a wide variety of electrical and electronic testing applications. This true-rms meter provides easy one-handed operation in a compact package.

#### Features include:

- Resistance, continuity, frequency, capacitance, and diode test
- Measures 10 A (20 A overload for 30 seconds)
- Large white LED backlight to work in poorly lit areas
- Compact ergonomic design for one-handed operation
- Compatible with optional magnetic hanger (ToolPak™)
- True-rms for accurate measurements on non-linear loads
- Min/Max/Average with elapsed time to record signal fluctuations
- CAT III 600 V safety rated

#### General specifications

Accuracy is specified for 1 year after calibration, at operating temperatures of 18 °C to 28 °C, with relative humidity at 0 % to 90 %.

The accuracy specifications take the form of:  
± ( [ % of reading ] + [ counts ] )

Maximum voltage between any terminal and earth ground	600 V
Surge protection	6 kV peak per IEC 61010-1 600 V CAT III, Pollution Degree 2
Fuse for A input	11 A, 1000 V FAST Fuse (Fluke PN 803293)
Display	Digital: 6,000 counts, updates 4/sec
Bar graph	33 segments, updates 32/sec
Operating temperature	-10 °C to + 50 °C
Storage temperature	-40 °C to + 60 °C
Battery	9 volt Alkaline, NEDA 1604A/ IEC 6LR61
Battery life	400 hours typical, without backlight

Actual size



## Accuracy specifications

Measurement	Range	Resolution	Accuracy ± ([% of reading] + [counts])
DC millivolts	600.0 mV	0.1 mV	0.5 % + 2
DC volts	6.000 V	0.001 V	0.5 % + 2
	60.00 V	0.01 V	
	600.0 V	0.1 V	
Auto volts	600.0 V	0.1 V	2.0 % + 3 (dc, 45 Hz to 500 Hz) 4.0 % + 3 (500 Hz to 1 kHz)
AC millivolts <sup>1</sup> true-rms	600.0 mV	0.1 mV	1.0 % + 3 (dc, 45 Hz to 500 Hz) 2.0 % + 3 (500 Hz to 1 kHz)
AC volts <sup>1</sup> true-rms	6.000 V	0.001 V	1.0 % + 3 (45 Hz to 500 Hz) 2.0 % + 3 (500 Hz to 1 kHz)
	60.00 V	0.01 V	
	600.0 V	0.1 V	
Continuity	600 Ω	1 Ω	Beeper on < 20 off > 250 ; detects opens or shorts of 500 μs or longer.
Ohms	600.0 Ω	0.1 Ω	0.9 % + 2
	6.000 kΩ	0.001 kΩ	
	60.00 kΩ	0.01 kΩ	
	600.0 kΩ	0.1 kΩ	0.9 % + 1
	6.000 MΩ	0.001 MΩ	
	40.00 MΩ	0.01 MΩ	5 % + 2
Diode test	2.000 V	0.001 V	0.9 % + 2
Capacitance	1000 nF	1 nF	1.9 % + 2
	10.00 μF	0.01 μF	
	100.0 μF	0.1 μF	
	9999 μF	1 μF	1.9 % + 2
	100 μF to 1000 μF		
	> 1000 μF		
Lo-Z capacitance	1 nF to 500 μF		10 % + 2 typical
AC amps true-rms (45 Hz to 500 Hz)	6.000 A	0.001 A	1.5 % + 3
	10.00 A	0.01 A	
	20 A overload for 30 seconds max.		
DC amps	6.000 A	0.001 A	1.0 % + 3
	10.00 A	0.01 A	
	20 A overload for 30 seconds max.		
Hz (V or A input) <sup>2</sup>	99.99 Hz	0.01 Hz	0.1 % + 2
	999.9 Hz	0.1 Hz	
	9.999 kHz	0.001 kHz	
	50.00 kHz	0.01 kHz	

**Notes:**

<sup>1</sup> All ac voltage ranges are specified from 1 % to 100 % of range. Because inputs below 1 % of range are not specified, it is normal for this and other true-rms meters to display non-zero readings when the test leads are disconnected from a circuit or are shorted together. For volts, crest factor of ≤ 3 at 4000 counts, decreasing linearly to 1.5 at full scale. AC volts is ac coupled and ac mV is dc coupled.

<sup>2</sup> Frequency is ac coupled, 5 Hz to 50 kHz for ac voltage. Frequency is dc coupled, 45 Hz to 5 kHz for ac current.

## Ordering information

**Fluke-115** Multimeter

**Included**

TL75 Test leads, holster, User's manual and 9 V battery (installed).



**Fluke. Keeping your world up and running.™**

**Fluke Corporation**

PO Box 9090, Everett, WA USA 98206

**Fluke Europe B.V.**

PO Box 1186, 5602 BD Eindhoven, The Netherlands

**For more information call:**

In the U.S.A. (800) 443-5853 or Fax (425) 446-5116  
 In Europe/M-East/Africa (31 40) 2 675 200 or Fax (31 40) 2 675 222  
 In Canada (800)-36-FLUKE or Fax (905) 890-6866  
 From other countries +1 (425) 446-5500 or Fax +1 (425) 446-5116  
 Web access: <http://www.fluke.com>

©2006-2009 Fluke Corporation. Specifications subject to change without notice. Printed in U.S.A. 2/2009 2634043 D-EN-N Rev C

**Modification of this document is not permitted without written permission from Fluke Corporation.**

## Fluke TLK-225 SureGrip™ Master Accessory Set

Includes all the SureGrip™ leads and probes in a handy six-pocket, roll-up pouch, along with TL224 test leads.



### Overview

Test leads are an integral part of the complete measurement system. Worn out test leads can cause inaccurate readings and pose serious shock or electrocution hazard. The Fluke TLK-225 SureGrip™ Master Accessory Set with 13 items is the perfect replacement kit that provides flexibility and comfort with all SureGrip™ leads and probes in a convenient six pocket, roll up pouch.

### Models

#### Model (1)

Model Name	Description
Fluke TLK225	Fluke TLK-225 SureGrip™ Master Accessory Set

### Accessories

#### Compatible Products (15)

Model Name	Description
<b><u>Fluke 1577</u></b>	Fluke 1577 Insulation Multimeter
<b><u>Fluke 175</u></b>	Fluke 175 True RMS Digital Multimeter
<b><u>Fluke 177</u></b>	Fluke 177 True RMS Digital Multimeter
<b><u>Fluke 179</u></b>	Fluke 179 True RMS Digital Multimeter
<b><u>Fluke 27 II</u></b>	Fluke 27 II Rugged Digital Multimeter
<b><u>Fluke 28 II Ex</u></b>	Fluke 28 II Ex Intrinsically Safe True RMS Digital Multimeter

---

<b><u>Fluke 28 II</u></b>	Fluke 28 II Rugged Digital Multimeter
<b><u>Fluke 287</u></b>	Fluke 287 True-RMS Electronics Logging Multimeter
<b><u>Fluke 289</u></b>	Fluke 289 True-RMS Industrial Logging Multimeter
<b><u>Fluke 43B</u></b>	Fluke 43B Single Phase Power Quality Analyzer
<b><u>Fluke 787</u></b>	Fluke 787 ProcessMeter™
<b><u>Fluke 789</u></b>	Fluke 789 ProcessMeter†
<b><u>Fluke 81438</u></b>	Fluke 81438 Digital Multimeter
<b><u>Fluke 83V</u></b>	Fluke 83V Average Responding Industrial Multimeter
<b><u>Fluke 87V</u></b>	Fluke 87V Industrial Multimeter

---