


## FEATURES

- **Annealed Copper Conductor:** Provides superior conductivity and durability
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and enhances cable longevity
- **Plain Conductor Type:** Ensures consistent electrical performance
- **24/0.2 Core Strands:** Delivers flexibility and ease of installation
- **Operating Temperature Range -15 °C to 70 °C:** Suitable for a wide range of environments
- **Voltage Rating 500 V:** Supports high voltage applications
- **White Jacket Colour:** Facilitates easy identification and routing
- **Outside Diameter 7.2 mm:** Compact design for space-saving installations

## RS PRO 0.75 mm<sup>2</sup> Flexible Cable, 50 m

RS Stock No: 606-061



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

This RS PRO flexible cable is designed for efficient electrical connectivity in various industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and durability. The cable is suitable for environments requiring flexibility and reliable performance.

## General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

## Mechanical Specifications

Cable CSA	0.75 mm <sup>2</sup>
Cable Length	50 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	2
Outside Diameter	7.2 mm

## Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

## Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	---

## Electrical Specifications

Voltage	500 V
---------	-------