



Brand of **NTN** corporation

Technical data

6307FT150ZZ


Single row deep groove ball bearings



TOPLINE deep groove ball bearing, radial contact, pressed steel cage, shields on both sides, applications up to 150°C.

TOPLINE

VISUAL (S)




NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

6307FT150ZZ

Single row deep groove ball bearings



PRODUCT DEFINITION	
Brand	SNR
d - Internal diameter	35 mm
D - External diameter	80 mm
B - Bearing/Inner ring width	21 mm
d1 - External diameter inner ring	46,2 mm
D1 - Inner diameter outer ring	70,1 mm
rs - Min fillet radius	1,5 mm
Radial clearance class	C3
Mass	0,446 kg

PRODUCT PERFORMANCE	
C - Dynamic load	35100000 mN
C0 - Static load	19200000 mN
Cu - Fatigue limit load	870000 mN

6307FT150ZZ

Single row deep groove ball bearings

PRODUCT PERFORMANCE

f0 - Coefficient	13.2
N lim - Mechanical Limit Speed	51000 °/s
Tmin - Min operating temperature	243,15 °K
Tmax - Max operating temperature	423,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	3.069 Hz
BPFI - Over rolling frequency on inner (60 rpm)	4.931 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	4.066 Hz
BRF - Rotational frequency - rolling element (60 rpm)	2.033 Hz
FTF - Rotational frequency - cage (60 rpm)	0.384 Hz

ABUTMENT

da min - Min shoulder diameter IR	43 mm
da max - Max shoulder diameter IR	46,2 mm
Da max - Max shoulder diameter OR	72 mm
ra max - Max shaft & housing fillet radius	1,5 mm



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$P = X.F_r + Y.F_a$

$\frac{f_0 F_a}{C_0}$	e	Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y
0.172	0.19	1	0	0.56	2.3
0.345	0.22				1.99
0.689	0.26				1.71
1.03	0.28				1.55
1.38	0.3				1.45
2.07	0.34				1.31
3.45	0.38				1.15
5.17	0.42				1.04
6.89	0.44				1

Equivalent static radial load

$P_0 = X_0.F_r + Y_0.F_a$

X_0	Y_0
0.6	0.5

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$

