



Switches > Rocker Switches



Switch Type: **High Power Rocker Switch**
Product Mount Type: **Panel Mount**
Indicator/Imprint Legend: **- =**
Panel Cutout Size: **21 x 36.5 mm [.835 x 1.441 in, .835 x 1.448 in, .835 x 1.456 in]**
Switch Contact Plating Material: **Silver Tin Oxide**

Features

Product Type Features

Switch Type	High Power Rocker Switch
Actuator Type	Top
Actuator Style	Rocker
Switch Connection Type	Quick Connect Terminal

Configuration Features

Indicator/Imprint Legend	- =
Panel Cutout Size	21 x 36.5 mm[.835 x 1.441 in][.835 x 1.448 in][.835 x 1.456 in]
Configuration (Pole-Throw)	Single Pole - Double Throw
Operating Function	On On

Electrical Characteristics

Contact Current Rating	20 A
Operating Voltage Range	125 – 250 VAC

Body Features

Product Orientation	Vertical
Actuator Color	Black

Contact Features

Terminal Tab Width	6.35 mm[.25 in]
Switch Contact Plating Material	Silver Tin Oxide



Mechanical Attachment

Product Mount Type	Panel Mount
--------------------	-------------

Housing Features

Process Sealed	Yes
----------------	-----

Operation/Application

Indicator Type	No Indicator
----------------	--------------

Industry Standards

Compatible With Approved Standards Products	UL E46765
---	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought





TE Part #2176412-8
5W XSM M/OX 5% 10R



TE Part #1-794106-0
20P MINI UMN L R/A HDR ASSY



TE Part #539960-1
AUSZ-WKZ,MICRO TIM.



TE Part #2176230-1
3522 0R0 5% 3W



TE Part #1571083-2
PRASC1-16F-BBR00=POWER ROCKER



TE Part #3-1676123-5
1/2W SM M/OX 5% 22R



TE Part #2035363-4
1X6 GENERATION Y ASSY KEYC CPA

Documents

Datasheets & Catalog Pages
SWITCHES_CORE_PROGRAM_CATALOG
English