

314-LE

✓ ACTIVE

TE Internal #: 037216-000
Industrial Label, Die-Cut, Permanent Pressure Sensitive Acrylic Adhesive, UL, 9.5 mm [.375 in] Width, 9.5 mm [.375 in] Height, White, Standard Labels
[View on TE.com >](#)



Identification & Labeling > Labels > Standard Labels > LE White Labels



Label Type: **Industrial Label**
Label Style: **Die-Cut**
Label Adhesive Type: **Permanent Pressure Sensitive Acrylic Adhesive**
Compatible With Agency/Standards Products: **UL**
Product Width: **9.5 mm [.375 in]**

[All LE White Labels \(11\)](#)

Features

Product Type Features

Label Type	Industrial Label
------------	------------------

Body Features

Primary Product Color	White
Primary Product Material	Polyester

Dimensions

Product Width	9.5 mm[.375 in]
Product Height	9.5 mm[.375 in]

Usage Conditions

Operating Temperature Range	-40 – 150 °C[-40 – 302 °F]
-----------------------------	----------------------------

Printer/Label Features

Number of Labels Across	16
Label Style	Die-Cut
Label Thickness	80 Micron

Industry Standards

Compatible With Agency/Standards Products	UL
---	----

Packaging Features



Packaging Method	Sheet
Other	
Label Adhesive Type	Permanent Pressure Sensitive Acrylic Adhesive

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts







Customers Also Bought




TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT




TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts




TE Part #DT04-2P
REC, 2P, GRY, N




TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL

Documents

Product Drawings

314-LE

English

Datasheets & Catalog Pages

IDENTIFICATION SELECTION GUIDE

English

LE White Polyester labels

English