

Residual current operated circuit breaker, 4-pole, Type B, short-time delayed, In: 25 A, 300 mA, Un AC: 400 V



Model	
Product brand name	SENTRON
Product designation	RCCB
Design of the product	Short-time delayed
General technical data	
Number of poles	4
Size of installation devices / acc. to DIN 43880	1
Protection against electrical shock	Finger and back-of-hand safe
Short-circuit current / of back-up fuse / maximum permissible	100 A
Short-circuit current rating	10 kA
circuit-breaker / Design	5SV3
Mechanical service life (switching cycles) / typical	10 000
Switching function / short-term delayed	Yes
Overvoltage category	III
Supply voltage	
Current / at AC / rated value	25 A
Supply voltage	

<ul style="list-style-type: none"> • at AC / rated value 	400 V
<ul style="list-style-type: none"> • for testing equipment / minimum 	195 V
Supply voltage frequency	
<ul style="list-style-type: none"> • rated value 	50 Hz

Protection class

Protection class IP	IP20, if the distribution board is installed, with connected conductors
---------------------	---

Switching capacity

Switching capacity current / according to IEC 61008-1 / rated value	0.8 kA
---	--------

Dissipation

Power loss [W] / for rated value of the current / at AC / in hot operating state / per pole	1.2 W
---	-------

Current

Tripping residual current / rated value	300 mA
Tripping residual / rated value / derated current	
<ul style="list-style-type: none"> • at 40 Cel 	25 A
<ul style="list-style-type: none"> • at 45 Cel 	25 A
<ul style="list-style-type: none"> • at 50 Cel 	25 A
<ul style="list-style-type: none"> • at 55 Cel 	25 A
<ul style="list-style-type: none"> • at 60 Cel 	25 A
<ul style="list-style-type: none"> • at 65 Cel 	25 A
<ul style="list-style-type: none"> • at 70 Cel 	25 A
Type of fault current	B
I ² t-value / permissible	41 000 A ² ·s
Surge current resistance / rated value	3 kA

Product details

Product feature / silicon-free	Yes
--------------------------------	-----

Connections

Connectable conductor cross-section / stranded	
<ul style="list-style-type: none"> • minimum 	0.75 mm ²
<ul style="list-style-type: none"> • maximum 	35 mm ²

Mechanical Design

Height	90 mm
Width	72 mm
Depth	70 mm
Installation depth	70 mm
Number of width units	4
Mounting type	DIN rail (REG)
Mounting position	any



Net weight	543 g
------------	-------

Environmental conditions

Ambient temperature	
<ul style="list-style-type: none"> • minimum • maximum 	<ul style="list-style-type: none"> -25 °C 45 °C
Ambient temperature / during storage	
<ul style="list-style-type: none"> • minimum permissible • maximum permissible 	<ul style="list-style-type: none"> -40 °C 75 °C

Certificates

Reference code	
<ul style="list-style-type: none"> • acc. to DIN EN 61346-2 • acc. to DIN EN 81346-2 	<ul style="list-style-type: none"> F F

General Product Approval	Declaration of Conformity	other	Railway
 VDE	 EG-Konf.	Miscellaneous	Confirmation
Miscellaneous		Miscellaneous	Vibration and Shock

Railway

[Confirmation](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5SV3642-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/5SV3642-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SV3642-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

