

Article No. : 6SL4113-0KP24-2BF0



Figure similar

Client order no. :
Order no. :
Offer no. :
Remarks :

Item no. :
Consignment no. :
Project :

Rated data

Input

Number of phases	3 AC	
Line voltage	380...415V / 440...500V (~20+10 %)	
Line frequency	50/60 Hz (47 ... 63 Hz)	
Voltage range (voltage class)	380 ... 415 V (400V IEC)	440 ... 500 V (480V NEC)
Rated current	73.0 A	60.0 A

Output

Number of phases	3 AC	
Voltage range (voltage class)	380 ... 415 V (400V IEC)	440 ... 500 V (480V NEC)
Rated power (LO)	37.00 kW	50.00 hp
Rated power (HO)	30.00 kW	40.00 hp
Rated current (LO)	75.0 A	65.0 A
Rated current (HO)	63.0 A	52.0 A
Rated current (IN)	77.0 A	66.7 A
Rated Current (SRM)	85.0 A	

Max. output current 126.0 A

Pulse frequency (factory setting) 4 kHz

Output frequency for vector control 0 ... 480 Hz

Output frequency for V/f control 0 ... 550 Hz

Overload capability

Low Overload (LO)

150% rated current (LO) for 3 s, followed by 110% rated current (LO) for 57 s in a 300 s cycle time

High Overload (HO)

200% rated current (HO) for 3 s, followed by 150% rated current (HO) for 57 s in a 300 s cycle time

Electronic power supply

Voltage 24 V (20.4 ... 28.8 V)

Current demand, max. 3.00 A

General tech. specifications

Power factor λ (typical)

Displacement factor $\cos \phi$ (typical) 0.98

Efficiency η 0.98

Sound pressure level (1m) 70 dB

Filter class (integrated) RFI suppression filter for Category C2

Communication

Communication PROFINET, Modbus TCP, EtherNet/IP

SINAMICS SDI Standard Operator Panel

User interface

Operator element version	Integrated SDI standard for monitoring and diagnostics
Interface design	RJ45 with 100 MBit/s Ethernet
Display design	1.4" graphic display
Screen resolution	128 x 160 Pixel

Inputs / outputs

Standard digital inputs

Number	6 (additionally 2 AI configurable as 2 DI)
Switching level: 0 → 1	11 V
Switching level: 1 → 0	5 V
Max. inrush current	4 mA
Number as rapid input	1 (DI5)

Fail-safe digital inputs

Number	1 (additionally 4 DI configurable as 2 FDI)
--------	---

Digital outputs

Number as relay changeover contact	2
Output (resistive load)	DC 30 V, max. 0.5 A
Number as transistor	1
Output (resistive load)	DC 30 V, max. 0.4 A

Analog inputs

Number	2 (Differential input)
Resolution	16 bit

Operating mode

Voltage bipolar	-10 ... 10 V
Voltage unipolar	0 ... 10 V
Current	0 ... 20 mA
Current monitored	4 ... 20 mA

Switching threshold as digital input

0 → 1	11 V
1 → 0	5 V

Data sheet for SINAMICS G220

Article No. : 6SL4113-0KP24-2BF0

Analog outputs

Number	1 (Non-isolated output)
--------	-------------------------

Operating mode

Voltage unipolar	0 ... 10 V
------------------	------------

Current	0 ... 20 mA
---------	-------------

Current monitored	4 ... 20 mA
-------------------	-------------

Motor temperature interface

1 input for motor temperature, connectable PTC, KTY 84, PT1000, and bimetal temperature switch

PTC interface

Short-circuit monitoring < 200Ωm, overtemperature>1650Ωm

KTY84 interface

Short-circuit monitoring < 500Ωm; wire breakage>2120Ωm; measurement current 2mA

PTC1000 interface

Short-circuit monitoring < 603Ωm; wire breakage>2120Ωm; measurement current 2mA

Closed-loop control techniques

V/f linear / square-law / parameterizable	Yes
---	-----

V/f with flux current control (FCC)	Yes
-------------------------------------	-----

V/f ECO linear / square-law	Yes
-----------------------------	-----

Sensorless vector control	Yes
---------------------------	-----

Vector control, with sensor	Yes
-----------------------------	-----

Encoderless torque control	Yes
----------------------------	-----

Torque control, with encoder	Yes
------------------------------	-----

Ambient conditions

Cooling	Air cooling using an integrated fan
---------	-------------------------------------

Cooling air requirement	0.058 m³/s (2.048 ft³/s)
-------------------------	--------------------------

Installation altitude (without derating)	1,000 m (3,281 ft)
--	--------------------

Max. ambient temperature with derating	50 °C
--	-------

Ambient temperature with high overload (without derating)	45 °C
---	-------

Ambient temperature with low overload (without derating)	40 °C
--	-------

Relative humidity during

Max. operation	95 %
----------------	------

Environmental conditions

Chemically active substances

Operation	Class 3C3, according to IEC 60721-3-3: 2002
-----------	---

Transport	Class 2C2 according to IEC 60721-3-2:1997 in marine- and weather-resistant transport packaging
-----------	---

Storage	Class 1C2 according to IEC 60721-3-1: 2002 in the transport packaging
---------	--

Biologically active substances

Operation	Class 3B1 according to IEC 60721-3-3: 2002
-----------	--

Transport	Class 2B1 according to IEC 60721-3-2:1997 in the transport packaging
-----------	---

Storage	Class 1B1 according to IEC 60721-3-1:1997 in the transport packaging
---------	---

Mechanically active substances

Operation	Class 3S2 according to IEC 60721-3-3: Ed. 2.2 2002 (Conductive dusts are not permitted.)
-----------	---

Climatic environmental conditions

Operation	Class 3K3 according to IEC 60721-3-3 Ed. 2.2: 2002
-----------	--

Transport	Class 2K4 according to IEC 60721-3-2:1997 in the transport packaging; temperature -40 ... +70 °C; relative atmospheric humidity 5..95% (without condensation)
-----------	--

Storage	Class 1K4 according to IEC 60721-3-1:1997 in the transport packaging; temperature -25 ... +55 °C; relative atmospheric humidity 5..95% (without condensation), storage altitude <=4000m; condensation, spray water, ice formation, salt mist not permissible
---------	---

Mechanical environmental conditions

Operation	Class 3M1 according to IEC 60721-3-3 Ed. 2.2: 2002
-----------	--

Transport	Class 2M3 according to IEC 60721-3-2:1997 in the transport packaging
-----------	---

Storage	Class 1M2 according to IEC 60721-3-1:1997 in the transport packaging
---------	---

Integrated Safety functions

Safety function "Safe Torque Off"	Yes
-----------------------------------	-----

Safe Stop 1 (SS1)	Yes
-------------------	-----

Safe Motor Temperature (SMT)	No
------------------------------	----

Extended software functions can be enabled with a license using an SD card.

Data sheet for SINAMICS G220

Article No. : 6SL4113-0KP24-2BF0

Connections

Signal cable

Type	Push-in connection
Conductor cross-section	0.20 ... 2.50 mm ² (24 ... 12 AWG)

Line side

Type	screw terminal
------	----------------

Conductor cross-section

for single-core cables	16.00 ... 50.00 mm ² (6 ... 1/0 AWG)
for multi-core cables	16.00 ... 50.00 mm ² (6 ... 1/0 AWG)

Motor end

Type	screw terminal
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)

DC link

Type	screw terminal
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)

PE connection

Type	M8, screw terminal
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)
Type	stud terminal, M6
Conductor cross-section	10.00 ... 50.00 mm ² (8 ... 1/0 AWG)

Max. motor cable length

Shielded	200 m (656 ft)
Unshielded	300 m (984 ft)

with EMC category C2

Shielded	150 m (492 ft)
----------	----------------

Mechanical data

Degree of protection	IP55 / UL type 12
Frame size	FSD2
Net weight	37.5 kg (82.67 lb)

Dimensions

Width	270 mm (10.63 in)
Height	650 mm (25.59 in)
Depth	283 mm (11.14 in)

Memory card

1 slot for SD card	SINAMICS SD card, 8GByte
--------------------	--------------------------

Certificates

Certificate of suitability	CE, KC, cULus (UL 61800-5-1, CSA 22.2 No. 274) , EAC, UKCA
----------------------------	--

CE marking

EMC directive 2014/30/EU; Low Voltage Directive 2014/35/EU; RoHS Directive 2011/65/EU; energy efficiency and eco design 2009/125/EU

Verification of suitability for fail-safety	SIL 3 according to IEC 61508 and IEC 61800-5-2, PL e according to ISO 13849-1, Category 4 according to ISO 13849-1
---	--

Environmental compatibility	RoHS II, REACH, Green Passport
-----------------------------	--------------------------------

Explosion protection	-
----------------------	---


shipbuilding approval	No
-----------------------	----

Converter losses to IEC61800-9-2*

Efficiency class	IE2
In scope of Ecodesign Directive	No (in the valid range)
Reason of exception	no exception

IEC power loss data based on

Input	3 AC 400 V, 50 Hz
Output	3 AC 0 - 400 V, 50 Hz, 4 kHz Space-vector modulation
Rated apparent power	53.3 kVA
Power loss in standby	35.2 W (0.1%)



Data sheet for SINAMICS G220

Article No. : 6SL4113-0KP24-2BF0

NEC power loss data based on


Input	3 AC 480 V, 60 Hz
Output	3 AC 0 - 480 V, 60 Hz, 4 kHz Space-vector modulation
Rated apparent power	55.5 kVA
Power loss in standby	35.2 W (0.1%)

the absolute power losses for motor voltages according to NEC (AC 230 V, AC 460 V, AC 575 V) are approximately 2 % lower

The percentage values show the losses in relation to the rated apparent power of the converter.

The diagram shows the losses for the points (as per standard IEC61800-9-2) of the relative torque generating current (I) over the relative motor stator frequency (f). The values are valid for the basic version of the converter without options/components.

*calculated values



Data sheet for SINAMICS G220

Article No. : 6SL4113-0KP24-2BF0

Data sheet for Option Module OM-DQ (Drive CLiQ)

Electrical data

Operating voltage (DC)	24.0 V (20.4 ... 28.8 V)
	External 24 V power supply required if 24 V supply via DRIVE-CLiQ
Current demand, max.	0.70 A
Power loss	2.4 W

Inputs / outputs

DRIVE-CLiQ interface

Number	2
	RJ45, 100Mbit/s

Mechanical data

Degree of protection	IP20 / UL open type
Net weight	71.8 g (2.53 oz)

Dimensions

Width	65.2 mm (2.57 in)
Height	44.8 mm (1.76 in)
Depth	38.3 mm (1.51 in)

Ambient conditions

Ambient temperature during

Operation	-20 ... 60 °C (-4 ... 140 °F)
Transport	-40 ... 70 °C (-40 ... 158 °F)
Storage	-25 ... 55 °C (-13 ... 131 °F)

Relative humidity

without condensation	95 %
----------------------	------

Certificates

Certificate of suitability	CU, cULus (UL 61800-5-1, CSA 22.2 No. 274), EAC, RoHS II, REACH, safety according to EC 61800-5-2 and ISO 13849-1, Green Passport
----------------------------	---

Environmental compatibility	RoHS II, REACH, Green Passport
-----------------------------	--------------------------------