




**Part Number :** [26606050](#)  
**Product Description :** KK 396 Solid Vertical Header,  
Friction Lock, with Snap-in Plastic Peg PCB Lock, 5  
Circuits, Tin (Sn) Plating  
**Series Number :** 42891  
**Status :** Active  
**Product Category :** PCB Headers and Receptacles  
**Engineering Number :** 42891-0005



## Documents & Resources

### Drawings

[026606050 sd.pdf](#)  
[PK-42491-001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)  
[Symbol and Footprint \(Multi-Format\)](#)  
[SYM-26-60-6050-001.zip](#)

### Specifications

[PS-08-50-001.pdf](#)

## Product Environment Compliance

### Compliance

|                    |                                                                                                              |
|--------------------|--------------------------------------------------------------------------------------------------------------|
| GADSL/IMDS         | Not Relevant                                                                                                 |
| China RoHS         | <br>per SJ/T 11365-2006 |
| EU ELV             | Not Relevant                                                                                                 |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21                                                                               |
| REACH SVHC         | Not Contained per D(2023)8585-DC<br>(23 Jan 2024)                                                            |
| EU RoHS            | Compliant per EU 2015/863                                                                                    |

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

|                |                                                                                                              |
|----------------|--------------------------------------------------------------------------------------------------------------|
| Status         | Active                                                                                                       |
| Category       | PCB Headers and Receptacles                                                                                  |
| Series         | 42891                                                                                                        |
| Description    | KK 396 Solid Vertical Header, Friction Lock, with Snap-in Plastic Peg PCB Lock, 5 Circuits, Tin (Sn) Plating |
| Application    | Power, Wire-to-Board                                                                                         |
| Component Type | PCB Header                                                                                                   |
| Product Name   | KK 396                                                                                                       |
| UPC            | 800754201759                                                                                                 |

### Agency

|    |        |
|----|--------|
| UL | E29179 |
|----|--------|

### Electrical

|                               |      |
|-------------------------------|------|
| Current - Maximum per Contact | 7.0A |
| Voltage - Maximum             | 250V |

### Physical

|                                |                           |
|--------------------------------|---------------------------|
| Breakaway                      | No                        |
| Circuits (Loaded)              | 5                         |
| Circuits (maximum)             | 5                         |
| Durability (mating cycles max) | 25                        |
| Flammability                   | 94V-0                     |
| Glow-Wire Capable              | No                        |
| Lock to Mating Part            | Yes                       |
| Material - Metal               | Brass                     |
| Material - Plating Mating      | Tin                       |
| Material - Plating Termination | Tin                       |
| Net Weight                     | 1.888/g                   |
| Number of Rows                 | 1                         |
| Orientation                    | Vertical                  |
| Packaging Type                 | Bag                       |
| PCB Locator                    | Yes                       |
| PCB Retention                  | Yes                       |
| PCB Thickness - Recommended    | 1.60mm                    |
| PC Tail Length                 | 3.56mm                    |
| Pitch - Mating Interface       | 3.96mm                    |
| Plating min - Mating           | 5.080µm                   |
| Plating min - Termination      | 5.080µm                   |
| Polarized to Mating Part       | No                        |
| Polarized to PCB               | Yes                       |
| Shrouded                       | No                        |
| Stackable                      | Yes                       |
| Temperature Range - Operating  | See Product Specification |
| Termination Interface Style    | Through Hole              |

### Solder Process Data

|                              |      |
|------------------------------|------|
| Max-Duration                 | 5    |
| Lead-Free Process Capability | WAVE |
| Max-Cycle                    | 1    |
| Max-Temp                     | 235  |

---

### Mates With / Use With

**Mates with Part(s)**

| Description                               | Part Number  |
|-------------------------------------------|--------------|
| KK 3.96mm Single Row Crimp Housings       | <u>2139</u>  |
| KK 3.96mm Single Row Crimp Housings       | <u>3069</u>  |
| KK 3.96mm Crimp Housings                  | <u>41695</u> |
| KK 396 PC Board Connector                 | <u>41815</u> |
| KK 3.96mm Pitch Single Row Crimp Housings | <u>6442</u>  |

---

This document was generated on Aug 05, 2025