

Eaton 189799

Catalog Number: 189799

Eaton Moeller series NZM - Molded Case Circuit Breaker. Shunt release for NZM2/3, 24AC/DC, Push-in terminals

General specifications



Product Name	Catalog Number
Eaton Moeller series NZM release	189799
EAN	Product Length/Depth
4015081877942	115 mm
Product Height	Product Width
65 mm	75 mm
Product Weight	Compliances
0.08 kg	IEC
	UL/CSA
	RoHS conform

Product specifications

Used with

NZM2(-4), N(S)2(-4)

NZM3(-4), N(S)3(-4)

Type

Accessory

Shunt release

Special features

When the shunt release is live, contact with the circuit-breaker's main contacts on switching on is reliably prevented.

Shunt release modules cannot be installed simultaneously with early-make contact NZM...-XHIV, undervoltage release NZM...-XU..., or relays modules NZM...-X2A...

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

Resources

Brochures

[eaton-digital-nzm-brochure-br013003en-en-us.pdf](#)

[eaton-feerum-the-whole-grain-solution-success-story-en-us.pdf](#)

Catalogs

[eaton-digital-nzm-catalog-ca013003en-en-us.pdf](#)

Declarations of conformity

[DA-DC-03_NZM2](#)

Installation instructions

[eaton-circuit-breaker-voltage-release-nzm2-3-il012141zu.pdf](#)

Installation videos

[Introduction of the new digital circuit breaker NZM](#)

[The new digital NZM Range](#)

Technical data sheets

[eaton-nzm-technical-information-sheet](#)

Wiring diagrams

[eaton-circuit-breaker-release-nzm-shunt-release-wiring-diagram.eps](#)

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

Electric connection type

Screw connection

Frame

NZM2/3

Number of contacts (normally open contacts)

0

Rated control supply voltage

24 V AC/DC

Rated control supply voltage (Us) at AC, 50 Hz - max

24 V

Rated control supply voltage (Us) at AC, 50 Hz - min

24 V

Rated control supply voltage (Us) at AC, 60 Hz - max

24 V

Rated control supply voltage (Us) at AC, 60 Hz - min

24 V

Suitable for

Motor safety switch

Off-load switch

Connection type

With push in terminal

Voltage type

AC

Rated control supply voltage (Us) at DC - max

24 V

Rated control supply voltage (Us) at DC - min

24 V

Number of contacts (normally closed contacts)

0

Number of contacts (change-over contacts)

0

Undelayed short-circuit release - min

0 A

Undelayed short-circuit release - max

0 A



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are
property of their respective
owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)