



Product designation  
Product type designation  
Motor type

Soft Starter  
ADXT  
Asynchronous  
three phase

**Electrical features**


Supplies voltage	Type of system		Three phase
	Rated supply voltage	V	380...690VAC
	auxiliary supply voltage (Us)		24VAC/DC
	Rated frequency	Hz	50/60
Rated starter current Ie		A	104
Rated motor power in-line			
	IEC ratings (T≤40°C)		
	400VAC	kW	55
	500VAC	KW	75
	690VAC	KW	90
	UL ratings (T≤40°C)		
	380-415VAC	HP	60
	440-480VAC	HP	75
	550-600VAC	HP	100
Rated motor power inside delta			
	IEC ratings (T≤40°C)		
	400VAC	kW	75
	500VAC	KW	110
	690VAC	KW	132
	UL ratings (T≤40°C)		
	380-415VAC	HP	75
	440-480VAC	HP	125
	550-600VAC	HP	150
Number of controlled phases		Nr.	3
Built-in bypass			Yes
Cooling System			Forced
Rated insulation voltage Ui		V	690
<b>Programming interface</b>			
Display			LCD graphic display
Programming with NFC technology			No
Optical port			No
<b>Startup and stop settings</b>			
Startup method			Constant current, current ramp, voltage ramp, adaptive control

Stop method	Voltage ramp, adaptive control, free-wheel stop, DC braking, soft stop with braking contactor
<b>Protections</b>	
Auxiliary supply protection	Voltage too low
Power supply Protection	No power, phase loss, phase sequence, frequency out of limits, voltage out of limits
Motor protection	Overload, locked rotor, current asymmetry, current too low, power too low, overtemperature, starting too long
Starter protection	Overcurrent, overtemperature, phase shorted
<b>Functions</b>	
Built-in bypass	Yes
Built-in display and keypad	Yes
Languages	6
View measurements	Yes
Torque control	No
Adjustable current limit	Yes
Dynamic braking	Yes
Kick Start function	Yes
Motor overload electronic protection	Yes
Motor protection PTC input	Thermistor input
Protection against phase loss	Yes
Protection against phase inversion	Yes
Protection against locked rotor	Yes
Protection against thyristor overtemperature	Yes
Protection against low load	Yes
Programmable alarm	Yes
Digital inputs	4
Analog inputs	0
Digital outputs	3
Analog output	1
Optical port for programming	No
Event log	Yes
Motor hour counter	Yes
Startup counter	Yes
Clock calendar	Yes
Remote external keypad	Yes

**Input and Output**

Digital inputs	Number of digital input	Nr.	4
----------------	-------------------------	-----	---

	Digital input type		4 input with dry contact + 1 thermistor input
	Digital input functions		1x Start/Stop, 1x Reset and 2 Programmable
<b>Digital outputs</b>			
	Number of digital output	Nr.	3
	Digital output arrangement		2x 1NO + 1x C/O 1NO Line contactor + 1NO Programmable + 1C/O Programmable
	Digital output functions		
<b>Ambient conditions</b>			
<b>Temperature</b>			
	Operating temperature	min	°C -10
		max	°C +60°C (with current derating >40°C)
	Storage temperature	min	°C -25
		max	°C +60
	Max altitude	m	1000 without derating
	Relative humidity	%	<95%
	Pollution degree		3
<b>Housing</b>			
	Mounting		Screw-fixing
	IP degree of protection		IP20
	Dimensions (W x H x D)	mm	152x336x233
	Weight	Kg	5.5
<b>Dimensions</b>			



### Certifications and compliance

#### Compliance

CSA C22.2 n°60947-4-2

IEC/EN/BS 60947-4-2

UL 60947-4-2

#### Certificates

cULus

RCM

### ETIM classification

ETIM 8.0

EC000640 - Soft  
starter