


**FAG****33205**

Tapered roller bearing

Tapered roller bearings 332, main dimensions to DIN ISO 355 / DIN 720, separable, adjusted or in pairs

Technical information



Your current product variant

Tolerance class	P6X	Class 6X (ISO 492:2014)
Heat treatment	Standard	
Cage	Standard	Sheet steel cage, window cage, roller-guided
Internal design	Standard	
Quality level	Standard	
Number of rolling element rows	1	Single-row design

Main Dimensions & Performance Data

d	25 mm	Bore diameter
D	52 mm	Outside diameter
B	22 mm	Width, inner ring
C	18 mm	Width, outer ring
T	22 mm	Width, total
C_r	48,500 N	Basic dynamic load rating, radial
C_{0r}	58,000 N	Basic static load rating, radial
C_{ur}	7,100 N	Fatigue load limit, radial
n_G	14,200 1/min	Limiting speed
n_{gr}	8,300 1/min	Thermal speed rating
m	218 g	Weight



Mounting dimensions

d _a max	30 mm	Maximum diameter of shaft shoulder
d _b min	31 mm	Minimum diameter of shaft shoulder
D _a min	43 mm	Minimum diameter of housing shoulder
D _a max	46 mm	Maximum diameter of housing shoulder
D _b min	49 mm	Minimum diameter of housing shoulder
C _a min	4 mm	Minimum axial space
C _b min	4 mm	Minimum axial space
r _a max	1 mm	Maximum fillet radius of shaft
r _b max	1 mm	Maximum fillet radius of housing

Dimensions

r _{1, 2} min	1 mm	Minimum chamfer dimension of inner ring back face
r _{3, 4} min	1 mm	Minimum chamfer dimension of outer ring back face
a	14 mm	Distance between the apexes of the pressure cones
d ₁	39.6 mm	Guidance rib diameter of inner ring

Temperature range

T _{min}	-30 °C	Operating temperature min.
T _{max}	120 °C	Operating temperature max.

Calculation factors

e	0.35	Limiting value of Fa/Fr for the applicability of diff. Values of factors X and Y
Y	1.71	Dynamic axial load factor
Y ₀	0.94	Static axial load factor

Additional information

T2DE025	Comparative designation to ISO 10317 and ISO 355
---------	--



Characteristics

-  Radial load
-  Axial load in one direction
-  Grease Lubrication
-  Oil Lubrication
-  Not sealed