

# SACC-M 8FS-3PL-M - Connector



1482523

<https://www.phoenixcontact.com/gb/products/1482523>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector, Universal, 3-position, unshielded, Socket straight M8, coding: A, Push-lock spring connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 3.5 mm ... 5.5 mm

## Your advantages

- Time-saving Push-Lock connection: Tool-free connection and disconnection of conductors by opening the contact levers
- Intuitive connection: Easy assignment of individual litz wires with color-coded and numerical identification of the contact levers
- Integrated Push-in Technology: Wire rigid and pretreated conductors easily by means of simple, direct insertion
- Shock- and vibration-resistant connection: Proven spring-cage technology guarantees secure and reliable contacting
- Safe use in the field, thanks to a high degree of protection

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1482523       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AF2BEA        |
| Product key                          | AF2BEA        |
| GTIN                                 | 4067923233461 |
| Weight per piece (including packing) | 16.2 g        |
| Weight per piece (excluding packing) | 22.22 g       |
| Customs tariff number                | 85366990      |
| Country of origin                    | DE            |

# SACC-M 8FS-3PL-M - Connector

1482523

<https://www.phoenixcontact.com/gb/products/1482523>



## Technical data

### Notes

|               |                                                                                                                                                                                                                                                                                              |
|---------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Assembly note | <b>NOTE:</b> Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.                                                      |
| General       | The user must take appropriate safety precautions so that the connector cannot be accidentally loosened or opened. To protect against unintentional opening of the connector, the thread must be secured between the housing and the connector head using a suitable cyanoacrylate adhesive. |


### Product properties

|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Sensor type          | Universal                       |
| Number of positions  | 3                               |
| No. of cable outlets | 1                               |
| Shielded             | no                              |
| Coding               | A                               |
| Cable outlet         | straight                        |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

|                     |                                                                                      |
|---------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing |  |
| Width               | 14 mm                                                                                |
| Height              | 14 mm                                                                                |
| Length              | 49 mm                                                                                |

### External dimensions

|                  |                   |
|------------------|-------------------|
| Outside diameter | 3.5 mm ... 5.5 mm |
|------------------|-------------------|

### Housing

|                  |       |
|------------------|-------|
| Diameter housing | 14 mm |
|------------------|-------|

### Material specifications

|                                        |                        |
|----------------------------------------|------------------------|
| Material                               | PBT                    |
|                                        | PA 6 (Actuation lever) |
| Flammability rating according to UL 94 | V0                     |
| Seal material                          | NBR                    |

# SACC-M 8FS-3PL-M - Connector



1482523

<https://www.phoenixcontact.com/gb/products/1482523>

|                               |                              |
|-------------------------------|------------------------------|
| Material of grip body         | PA 6.6                       |
| Contact material              | CuSn                         |
| Contact surface material      | Ni/Au                        |
| Contact carrier material      | PA 6.6                       |
| Material for screw connection | Zinc die-cast, nickel-plated |

## Connection data

### Conductor connection

|                                         |                                              |
|-----------------------------------------|----------------------------------------------|
| Connection method                       | Push-lock spring connection                  |
| Connection cross section                | 0.14 mm <sup>2</sup> ... 0.5 mm <sup>2</sup> |
| Connection cross section AWG            | 26 ... 20                                    |
| Stripping length of the individual wire | 7 mm                                         |
| Tightening torque                       | 0.2 Nm (M8 knurl)                            |
|                                         | 0.2 Nm (Connector with coupling sleeve)      |
|                                         | 1.5 Nm (Pressure nut with coupling sleeve)   |

### Pin assignment

|                                                           |        |
|-----------------------------------------------------------|--------|
| Contact   Color (signal designation)   Contact (optional) | 1 = BN |
|                                                           | 3 = BU |
|                                                           | 4 = BK |

## Electrical properties

|                                |         |
|--------------------------------|---------|
| Nominal voltage U <sub>N</sub> | 48 V AC |
|                                | 60 V DC |
| Nominal current I <sub>N</sub> | 4 A     |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Socket   |
| Head cable outlet | straight |
| Head thread type  | M8       |
| Coding            | A        |

## Cable/line

|                                         |           |
|-----------------------------------------|-----------|
| Signal type/category                    | Universal |
| Stripping length of the individual wire | 7 mm      |

## Environmental and real-life conditions

### Ambient conditions

# SACC-M 8FS-3PL-M - Connector



1482523

<https://www.phoenixcontact.com/gb/products/1482523>

|                                 |                                  |
|---------------------------------|----------------------------------|
| Degree of protection            | IP65                             |
|                                 | IP67                             |
| Ambient temperature (operation) | -25 °C ... 85 °C (Plug / socket) |

## Standards and regulations

M8

|                          |                 |
|--------------------------|-----------------|
| Standard designation     | M8 connector    |
| Standards/specifications | IEC 61076-2-104 |

# SACC-M 8FS-3PL-M - Connector


1482523

<https://www.phoenixcontact.com/gb/products/1482523>




## Drawings


Dimensional drawing



Functional drawing



Schematic diagram



Pin assignment of M8 socket, 3-pos., view of pin side

# SACC-M 8FS-3PL-M - Connector

1482523

<https://www.phoenixcontact.com/gb/products/1482523>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440116 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

# SACC-M 8FS-3PL-M - Connector

1482523

<https://www.phoenixcontact.com/gb/products/1482523>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)