



Part Number : [2044731134](#)

Product Description : DDR5 RDIMM Socket, Vertical Surface Mount, 0.38µm Gold Plating, 288 Circuits, PCB Thickness 1.57mm to 3.18mm, Black Housing, Black Latch, with Pick and Place Tape

Series Number : 204473

Status : Active

Product Category : Memory Module Connectors



Documents & Resources

Drawings

[2044731134 sd.pdf](#)

[2044730003-000.pdf](#)

[2044730000-000.pdf](#)

[2044730000-000.zip](#)

Specifications


[2044730000-AS-000.pdf](#)

[2044730002-000.pdf](#)

[2044730002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS

- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Memory Module Connectors
Series	204473
Description	DDR5 RDIMM Socket, Vertical Surface Mount, 0.38µm Gold Plating, 288 Circuits, PCB Thickness 1.57mm to 3.18mm, Black Housing, Black Latch, with Pick and Place Tape
Component Type	Socket
JEDEC Outline	MO-329
Product Name	DDR5 DIMM
UPC	191128978828

Agency

CSA	1409726
UL	E29179

Electrical

Current - Maximum per Contact	1.0A
Voltage - Maximum	29V AC (RMS)/DC

Physical

Circuits (Loaded)	288
Circuits (maximum)	288
Durability (mating cycles max)	25
Entry Angle	Vertical (Top Entry)
Flammability	94V-0
Housing Color	Black
Keying to Mating Part	Yes
Latch Color	Black
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Polyamide
Net Weight	6.287/g
Packaging Type	Tray
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.57mm, 3.18mm
Pitch - Mating Interface	0.85mm
Pitch - Termination Interface	0.85mm
Plating min - Mating	0.380µm
Plating min - Termination	2.540µm
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Surface Mount

Solder Process Data

Max-Duration	10
Lead-Free Process Capability	REFLOW
Max-Cycle	3
Max-Temp	260

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Memory Module Cards of 1.27mm

	Thickness
--	-----------

This document was generated on Nov 05, 2025