

## Features

- UL approved Nylon 66
- UL94V-2 flame rated
- Low Smoke, Halogen Free
- Max operating temperature 85°C

## RS PRO Cable Ties

RS Stock No.: 0828986



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

## Product Description

Designed for demanding cable management tasks, this cable tie offers exceptional strength and reliability. Made from fire-resistant Nylon 66 (UL-approved) with a flame-rating of 94V-2, it's built to deliver robust performance even in harsh environments. Whether in construction, telecom, data centres, or high-power installations, this cable tie helps keep things neat, safe, and resilient.

## General Specifications

|                                      |                                                        |
|--------------------------------------|--------------------------------------------------------|
| <b>Series</b>                        | Nylon Cable Ties                                       |
| <b>Type</b>                          | Non-Releasable                                         |
| <b>Colour</b>                        | Black                                                  |
| <b>Material</b>                      | Nylon 66                                               |
| <b>Finish</b>                        | Smooth                                                 |
| <b>Application</b>                   | Designed for quick installation and bundling of cables |
| <b>Resistant To</b>                  | Not specified                                          |
| <b>UV Resistant</b>                  | No                                                     |
| <b>Minimum Operating Temperature</b> | Not specified                                          |
| <b>Maximum Operating Temperature</b> | 85°C                                                   |
| <b>Fire Behaviour</b>                | Self-Extinguishing                                     |
| <b>Quantity</b>                      | 100                                                    |

## Mechanical Specifications

|                         |        |
|-------------------------|--------|
| <b>Length</b>           | 1530mm |
| <b>Width</b>            | 12.7mm |
| <b>Tensile Strength</b> | 1112N  |

## Approvals

|                     |      |
|---------------------|------|
| <b>Declarations</b> | RoHS |
|---------------------|------|

|               |    |
|---------------|----|
| Standards Met | UL |
|---------------|----|

