

Eaton 125D200

Catalog Number: 125D200

Fuse-link, low voltage, 125 A, AC 500 V, D5, 56 x 46 mm, gL/gG, DIN, IEC, time-delay

General specifications



Product Name	Catalog Number
Eaton Bussmann series low voltage D fuse	125D200
	EAN
	5027590429726

Product Length/Depth	Product Height
164 mm	164 mm

Product Width	Product Weight
110 mm	223.6 g

Compliances	Certifications
CE	IEC/EN 60269-3
RoHS Compliant	VDE 0636
CE Marked	IEC 60269
	DIN EN 60269-3 (VDE 0636 Part 30)
	DIN EN 60269-1 (VDE 0636 Part 10)
	DIN VDE 0636-301

Product specifications

Type

Fuse

Application

For domestic and general industrial applications

Amperage Rating

125 A

Fuse size

DV

Breaking capacity

50 kA

Construction size (fuse inserts)

DV

Rated voltage AC

500 V

Class

Class C gL/gG

Fuse type

D200 - Time delay

Accessory/spare part type

125GD200 Yellow screw cap gauge piece

Utilization category

gG (cable protection/equipment protection)

Color

Yellow

Interrupt rating

50 kAIC

Fuse indicator

Non-indicating

Connection

Other

Construction

D5

Construction size

DV

Fuse shape

Resources

Brochures

[eaton-bussmann-series-d-and-d0-fuses-product-aid-pa132014en-en-us.pdf](#)

Catalogs

[CA134002EN](#)

Technical service bulletins

[Datasheet - 125D200](#)

Bottle

Response time

Time-delay

Suitable for

R2/DV Fuse base

Material

White ceramic body

Release characteristic

Time-lag

Voltage rating

500 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia