



Part Number : [347360027](#)
Product Description : 2.54mm Pitch MX64 Terminal,
Silver Plating, 0.50-0.75mm², Left Reel Payoff, Also
used with MX123 Female Receptacle Housing
Series Number : 34736
Status : Active
Product Category : Crimp Terminals

Documents & Resources

Drawings


[347360027 sd.pdf](#)
[PK-31302-480-001.pdf](#)

Specifications

[AS-33468-002-001.pdf](#)
[PS-33468-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34; 33
China RoHS	 per SJ/T 11365-2006
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	34736
Description	2.54mm Pitch MX64 Terminal, Silver Plating, 0.50-0.75mm ² , Left Reel Payoff, Also used with MX123 Female Receptacle Housing
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff
Product Name	MX123,MX64
UPC	884982893818

Physical

Gender	Female
Material - Metal	Copper
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	0.236/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.905µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.50-2.06mm
Wire Size (AWG)	N/A

Wire Size mm ²	0.50-0.75
---------------------------	-----------

Mates With / Use With

Use with Part(s)

Description	Part Number
MX64 Sealed Single Row Receptacle Housings	<u>31403</u>
MX123 Receptacle Housings	<u>34566</u>
MX123 Female Receptacle Housings	<u>34576</u>

Application Tooling

Global

Description	Part Number
Hand Tool for MX64 ISO Terminal	<u>638258400</u>
FineAdjust Applicator for MX64 ISO Terminal	<u>639025300</u>