



PRODUCT-DETAILS

# SUP403M-K15

## Miniature Circuit Breaker - SUP400M - 1P - 15 A - K



### General Information

Extended Product Type	SUP403M-K15
Product ID	2CCG000131R0001
EAN	7612271506735
Catalog Description	Miniature Circuit Breaker - SUP400M - 1P - 15 A - K
Long Description	ABB Miniature circuit breaker SMISLINE TP, configurations (1P,2P,3P), Tripping characteristic K, Rated breaking capacity acc. UL489 10kA

### ABB EcoSolutions

ABB EcoSolutions	Yes
Recyclability Rate of the Product acc. to EN45555	Design for Closing Resource Loops - Standard EN45555 - 87.86 %
ABB Site Meeting Group Waste To Landfill Target	No non-hazardous waste is sent to a landfill
Sustainable Material Content in Packaging (wt. %)	0 % FSC Mix Cardboard - 2.62 % FSC Mix Cardboard - 15.76 % FSC Mix Cardboard - 43.57 % FSC Mix Cardboard - 32 % FSC Recycled Cardboard - 5.85 %
Extended Product Lifetime	Product Durability

End Of Life Disassembling Instructions	9AKK108469A6819
Environmental Product Declaration - EPD	9AKK108469A5736

## Technical

Rated Ultimate Short-Circuit Breaking Capacity ( $I_{cu}$ )	(230 V) 40 kA (400 V) 40 kA
Rated Service Short-Circuit Breaking Capacity ( $I_{cs}$ )	(240 V AC) 20 kA (415 V AC) 20 kA (480Y / 277 V AC) 10 kA
Rated Service Short-Circuit Breaking Capacity, in % of $I_{cu}$ ( $I_{cs}$ )	50 %
Power Supply Connection	Arbitrary
Contact Position Indication	Red ON / Green OFF
Energy Limiting Class	3
Electrical Endurance	10000 cycle
Mechanical Endurance	10000 cycle
Number of Protected Poles	1
Number of Poles	1P
Tightening Torque	2.8 N·m
Actuator Marking	I / O
Recommended Screw Driver	Pozidriv 2
Accessories Available	Yes
Number of Batteries	0
Connecting Capacity	Flexible 0.75 ... 25 mm <sup>2</sup> Rigid 0.75 ... 35 mm <sup>2</sup>

## Electrical

Tripping Characteristic	K
Rated Operational Voltage	acc. to IEC 60898-1 480 V
Rated Insulation Voltage ( $U_i$ )	acc. to IEC/EN 60664-1 500 V
Rated Impulse Withstand Voltage ( $U_{imp}$ )	4 kV
Input Voltage Type	AC
Rated Current ( $I_n$ )	15 A
Rated Frequency (f)	50 ... 60 Hz
Power Loss	5.1 W
Overvoltage Category	III

## Material Compliance

RoHS Declaration	2CCC005091D0201
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
RoHS Date	20240221
REACH Declaration	9AKK108467A9561
REACH Information	True - contains substances > 0.1 mass percentage
REACH Date	20230417
Conflict Minerals Reporting Template (CMRT)	9AKK108468A3363
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

WEEE B2C / B2B

Business To Business

---

**Environmental**


---

Ambient Air Temperature	Operation -25 ... 60 °C
Reference Ambient Air Temperature	40 °C
Degree of Protection	IP20
Pollution Degree	2
Resistance to Vibrations	1 mm 2 ... 13.2 Hz
Environmental Information	9AKK108467A9561

---



---

**Dimensions**


---

Width in Number of Modular Spacings	54
Product Net Width	54 mm
Product Net Height	102 mm
Product Net Depth / Length	74.5 mm
Product Net Weight	360 g
Built-In Depth (t <sub>2</sub> )	102 mm

---



---

**Engineering**


---

EPLAN Data	9AAF602870 EPLAN
------------	------------------

---



---

**Ordering**


---

Package Level 1 Units	carton 3 piece
Package Level 1 Gross Weight	1146 g

---



---

**Certificates and Declarations**


---

Declaration of Conformity - CE	No declaration needed
--------------------------------	-----------------------

---



---

**Installation**


---

Instructions and Manuals	2CCR330488B0001
Mounting Position	Any

---



---

**Popular Downloads**


---

Data Sheet, Technical Information	9AKK107492A6192
-----------------------------------	-----------------

---



---

**External Classifications and Standards**


---

ETIM 9	EC000042 - Miniature circuit breaker (MCB)
ETIM 10	EC000042 - Miniature circuit breaker (MCB)
UNSPSC	39121603

---

eClass	V11.0 : 27141901
IDEA Granular Category Code (IGCC)	4899 >> Miniature circuit breaker (MCB) screw-in model
Object Classification Code	F

**Accessories**

Identifier	Description	Type	Quantity	Unit Of Measure
2CDS200914R0001	S2C-H6RU Auxiliary Contact 1CO, UL489	HK400 S2C-H6RU11-L	1	piece
2CDS200924R0001	S2C-S6RU Signal Contact UL489	S2C-S6RU	1	piece
2CCA703488R0001	Dummy Housing (right side)	E210-DHR	1	piece

**Categories**

Low Voltage Products and Systems → Modular DIN Rail Products → Plug-in Distribution Systems → Plug-in Distribution Systems → Miniature Circuit Breakers MCBs

