

Eaton 265579

Catalog Number: 265579

Eaton Distribution parts. Pre-selection relay, 230VAC/50Hz, 4N/O, 20A, 2HP

General specifications



Product Name

Eaton Distribution parts

EAN

4015082655792

Product Height

70 mm

Product Weight

0.263 kg

Catalog Number

265579

Product Length/Depth

80 mm

Product Width

35 mm

Compliances

RoHS conform



Powering Business Worldwide

Product specifications

Amperage Rating

20 A

Mounting method

DIN rail

Equipment heat dissipation, current-dependent

10.4 W

Control voltage 1 type

AC

Ambient operating temperature - max

45 °C

Ambient operating temperature - min

-20 °C

Control voltage 1 - max

230 V

Control voltage 1 - min

230 V

Control voltage 2 - max

0 V

Control voltage 2 - min

0 V

Frequency control voltage 1 - max

50 Hz

Frequency control voltage 1 - min

50 Hz

Frequency control voltage 2 - max

0 Hz

Frequency control voltage 2 - min

0 Hz

Heat dissipation per pole, current-dependent

2 W

Incandescent lamp load - max

0 W

Load fluorescent lamp - max

0 VA

Load fluorescent lamp (duo circuit) - max

Resources

Declarations of conformity

[DA-DC-03_N2](#)

[DA-DC-03_Z-TN](#)

Drawings

[eaton-3d-drawing-r-pack.jpg](#)

[eaton-3d-drawing-z-r-sch-einbau.jpg](#)

[eaton-dimensions-mas-z-tn.jpg](#)

Wiring diagrams

[Z_TN_2MU_4S](#)

0 VA

Load fluorescent lamp (parallel compensated) - max

0 VA

Number of contacts (change-over contacts)

0

Number of contacts (normally closed contacts)

0

Number of contacts (normally open contacts)

4

Control voltage 2 type

AC/DC

Rated operational current for specified heat dissipation (In)

20 A

Supply voltage - max

250 V

Supply voltage - min

250 V

Switching current (cos phi = 0.6) - max

0 A

Width in number of modular spacings

2

Built-in depth

60 mm

Voltage type

AC

Functions

Mechanical

Reserved.

owners.

[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)