




ITV1000/2000/3000, Electro-Pneumatic Regulator ITV2030-33F3BN3

Datasheet

- Pressure range: 0.005 to 0.9 MPa
- Maximum flow rate: 4000 l/min (ANR)
- Port sizes: 1/8, 1/4, 3/8, 1/2
- Applicable fieldbus protocols: IO-Link, CC-Link, DeviceNet™, PROFIBUS, RS-232C.


Electro-pneumatic regulator

Standard specifications

Model	20 (1500 L/min)
Pressure Range	3 (0.005~0.5 MPa)
Power Voltage	0 (24VDC)
Input Signal	3 (Voltage Style 0~10VDC)
Monitor Output	3 (Switch Output PNP)
Thread	F (G[PF])
Port Size	3 (3/8 [2000,3000])
Accessory	B (Flat Bracket)
Cable Connector	N (w/oCable Connector)
Pressure Display Unit	3 (Bar)
Options	None
Maximum temperature of pressure medium	50 °C
Minimum temperature of pressure medium	0 °C
Maximum operating pressure	1.0 MPa
Minimum operating pressure	0.1 MPa
Maximum ambient temperature	50 °C
Minimum ambient temperature	0 °C
Approvals	CE
Protection class with connector	IP65
Flow rate of secondary exhaust	1500 NI/min

Min. supply pressure	Set pressure +0.1 MPa
Accuracy	±2%F.S. ±1 digit
Output signal Switch	PNP open collector output: Max. 80 mA
Weight	0.418 Kg

Dimensions



Additional information

Catalogue	ITV-G_EU.pdf
Declaration of conformity	DoC_ITVx_TF00023-B.pdf newDoC_ITV2_TF1Y002EN.pdf newDoC_ITV2000_3000_TF1Y106EN.pdf newDoC_ITV2000_3000_TF1V093EN.pdf
Installation manuals	IM_ITV2-IL-TF2Z014EN.pdf IMM_ITV3000_54GB-A.PDF IM_ITV2-IO_SMY17EN.pdf IMM_ITVx_TF112GB-A.pdf
Operation manuals	OM_ITV2_CC-Link_EN-B.pdf OM_ITV2_OM00068EN-C.pdf om_itv000_om005en-e.pdf OM_ITV2_RS-232C_EN.pdf OM_ITV2_OM00109EN-C.pdf OM_ITV2_DeviceNet_EN-C.pdf OM_ITV2_OM00112EN-C.pdf OM_ITV2_PROFIBUS-DP_EN-A.pdf