

# C-RC 95/M10 DIN - Ring cable lug



3240121

<https://www.phoenixcontact.com/gb/products/3240121>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Ring cable lug, non-insulated, 95 mm<sup>2</sup>, M10

## Your advantages

- The CRIMPFOX-RC... tools from our CRIMPFOX range of crimping pliers are available for optimum crimping
- The hard-soldered press zone enables maximum conductor pull-out values to be achieved
- The ring cable lugs without plastic sleeve are made from high-quality tin-plated electrolytic copper for maximum protection against corrosion

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 3240121             |
| Packing unit                         | 50 pc               |
| Minimum order quantity               | 50 pc               |
| Sales key                            | BH3422              |
| Product key                          | BH3422              |
| Catalog page                         | Page 491 (C-3-2019) |
| GTIN                                 | 4046356453387       |
| Weight per piece (including packing) | 40.38 g             |
| Weight per piece (excluding packing) | 40 g                |
| Customs tariff number                | 85369010            |
| Country of origin                    | CN                  |

# C-RC 95/M10 DIN - Ring cable lug

3240121

<https://www.phoenixcontact.com/gb/products/3240121>



## Technical data

### Product properties

|                  |                               |
|------------------|-------------------------------|
| Product type     | Connector                     |
| Product property | Design according to DIN 46234 |
|                  | Brazed                        |
|                  | Tin-plated                    |

### Dimensions

|                                                            |                                                                                    |
|------------------------------------------------------------|------------------------------------------------------------------------------------|
| Dimensional drawing                                        |  |
| Width                                                      | 24 mm                                                                              |
| Sleeve length                                              | 54 mm                                                                              |
| Length of the insulating material sleeve                   | 20 mm                                                                              |
| Maximum stripping length                                   | 23 mm                                                                              |
| Distance from the center to the insulating material sleeve | 22 mm                                                                              |
| Min. material thickness                                    | 2.5 mm                                                                             |
| Inner dimensions of the insulating collar                  | 15 mm                                                                              |

### Internal dimensions

|                   |         |
|-------------------|---------|
| Internal diameter | 10.5 mm |
|-------------------|---------|

### Material specifications

|          |                |
|----------|----------------|
| Color    | silver-colored |
| Material | Copper         |
| Coating  | tin-plated     |

### Mechanical properties

#### Technical data

|               |       |
|---------------|-------|
| Sleeve length | 54 mm |
|---------------|-------|

### Environmental and real-life conditions

#### Ambient conditions

|                                 |        |
|---------------------------------|--------|
| Ambient temperature (operation) | 110 °C |
|---------------------------------|--------|

### Standards and regulations

|                              |           |
|------------------------------|-----------|
| Design according to standard | DIN 46234 |
|------------------------------|-----------|

# C-RC 95/M10 DIN - Ring cable lug

3240121

<https://www.phoenixcontact.com/gb/products/3240121>



## Drawings

Dimensional drawing



# C-RC 95/M10 DIN - Ring cable lug



3240121

<https://www.phoenixcontact.com/gb/products/3240121>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27400204 |
|-------------|----------|

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001052 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

# C-RC 95/M10 DIN - Ring cable lug



3240121

<https://www.phoenixcontact.com/gb/products/3240121>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)