

19446000	DATA SHEET	
Valid from: 26.05.2025	EPIC® H-A 10 TG/TS	

Description

- The standard for housings. Large selection of different inserts.
- Easy-to-grip, user-friendly design makes it easy to plug and unplug the connector.



General Characteristics

Series	H-A 10
Locking	pins for single lever
Cable entry	top / side
Protection (DIN EN 60529)	IP 65 (latched)
Protection (NEMA 250, UL50E)	4, 12 (latched)
Temperature Range	-40°C to +125°C

Materials and Surfaces

Housing	aluminium alloy, powder-coated, grey
Gasket	NBR

Approvals

UL-Approval, E-File-Number	E75770
----------------------------	--------

Standard

Safety Standard	IEC 61984
-----------------	-----------

Versions


Article number	Article description	Thread M	Cable entry
19446000	EPIC® H-A 10 TG M20	M20x1,5	top
19446100	EPIC® H-A 10 TG M25	M25x1,5	top
44700043	EPIC® H-A 10 TG 2 x M20	2 x M20x1,5	top
44700008	EPIC® H-A 10 TS M20	M20x1,5	side
19445500	EPIC® H-A 10 TS M25	M25x1,5	side

Creator: TODV1/BU EPIC Released: VACH1/BU EPIC	Document: DB19446000EN Version: 02	Page 1 of 2
---	---------------------------------------	-------------



19446000	DATA SHEET	
Valid from: 26.05.2025	EPIC® H-A 10 TG/TS	

Technical Drawings

Top cable entry



Side cable entry



Industrial machinery and plant engineering



Mechanical resistance



Robust



Waterproof



Automation

Info

Universal, robust metal housings size H-A 10

Application range

Plant engineering, Light & sound technology, Plastics industry

Remark

Photographs are not to scale and do not represent detailed images of the respective products.

Creator: TODV1/BU EPIC Released: VACH1/BU EPIC	Document: DB19446000EN Version: 02	Page 2 of 2
---	---------------------------------------	-------------