

1412011
<https://www.phoenixcontact.com/gb/products/1412011>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact carrier, Ethernet/PROFINET CAT5 (100 Mbps), 4-position, Pin, straight, M12, coding: D, PCB mounting, SMD reflow, this item is undergoing a smooth changeover, lead-free alternative in accordance with RoHS II without exception 6c (Pb < 0.1%) possible on request in advance

Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Packaging available for automated pick and place assembly
- All common pin assignments and codings available
- Easy device integration thanks to mechanical port screw connections with threaded attachment, press-in contour or direct integration in the front plate
- Optional shield connection and seal for the device when not plugged in

Commercial data

Item number	1412011
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	ABQBGB
Product key	ABQBGB
GTIN	4046356992848
Weight per piece (including packing)	6.987 g
Weight per piece (excluding packing)	3.353 g
Customs tariff number	85366990
Country of origin	DE

SACC-CIP-M12MSD-4P SMD SH R32 - Contact carrier



1412011

<https://www.phoenixcontact.com/gb/products/1412011>

Technical data

Notes

Notes on operation	The electrical and mechanical data specified assume that the connector pair is correctly locked and mounted. If the connector is unlocked and if there is a danger of contamination, the connector must be sealed using a protective cap > IP54. Influences arising from litz wires, cables or PCB assembly must also be taken into consideration.
--------------------	--

Product properties

Product type	Contact insert
Application	Signal
Sensor type	Ethernet/PROFINET
Number of positions	4
Seal present	yes
Shielded	yes
Coding	D
Thread type	M12

Insulation characteristics

Overvoltage category	II
Degree of pollution	3

Electrical properties

Rated surge voltage	2.5 kV
Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage U_N	250 V
Nominal current I_N	4 A
Transmission characteristics (category)	CAT5 (IEC 11801:2002)

Connection data

Connection method	SMD reflow
-------------------	------------

Interfaces

Signal type/category	Ethernet/PROFINET CAT5, 100 Mbps
----------------------	----------------------------------

Material specifications

Flammability rating according to UL 94	V0
Seal material	FKM
Contact material	CuZn
Contact surface material	Au
Contact carrier material	PA

Connector

SACC-CIP-M12MSD-4P SMD SH R32 - Contact carrier



1412011

<https://www.phoenixcontact.com/gb/products/1412011>

Connection 1

Head design	Pin
Head cable outlet	straight
Head thread type	M12
Coding	D

Cable/line

Signal type/category	Ethernet/PROFINET CAT5, 100 Mbps
----------------------	----------------------------------

Mechanical properties

Mechanical data

Insertion/withdrawal cycles	> 100
-----------------------------	-------

Environmental and real-life conditions

Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 105 °C (Plug / socket) -55 °C ... 105 °C (without mechanical actuation)
UL Type Rating	Type 4 (indoor use only)

Standards and regulations

Standard designation	M12 circular connector
Standards/specifications	according to IEC 61076-2-101

Mounting

Mounting type	PCB mounting
---------------	--------------

Packaging specifications

Type of packaging	Belt
Delivery state	with assembly pad


SACC-CIP-M12MSD-4P SMD SH R32 - Contact carrier

1412011

<https://www.phoenixcontact.com/gb/products/1412011>

Drawings

Schematic diagram



Pin assignment M12 male connector, 4-pos., D-coded, male side


SACC-CIP-M12MSD-4P SMD SH R32 - Contact carrier



1412011
<https://www.phoenixcontact.com/gb/products/1412011>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1412011>

<div> cULus Recognized Approval ID: E221474-20160506</div>				
	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	250 V	4 A	-	-

SACC-CIP-M12MSD-4P SMD SH R32 - Contact carrier



1412011
<https://www.phoenixcontact.com/gb/products/1412011>

Classifications

ECLASS

ECLASS-13.0	27440110
-------------	----------

ETIM

ETIM 9.0	EC003557
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SACC-CIP-M12MSD-4P SMD SH R32 - Contact carrier



1412011

<https://www.phoenixcontact.com/gb/products/1412011>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	a5a57ae8-6ba7-4b48-a43c-239497027205

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk