



E32-T14 2M

Fiber optic sensor head, through-beam, long distance detection, square, side-view, R25 fiber, 2 m cable

Specifications

Sensing method	Through-beam
Shape	Square
Product Width (unpacked)	10.5 mm
Product Depth (unpacked)	8 mm
Product Height (unpacked)	25.2 mm
Application	Long distance detection
Temperature range	-40-70 °C
Sensing distance	4000 mm
Cable length	2 m
Bending radius	25 mm
Free cut	✓
Material core	Plastic
Degree of protection (IP)	IP67
Sensing surface orientation	Side-view
Material sheath	Polyethylene

Related products



E3X-ZV and E3X-MZV

Smart Fiber Amplifier



E3NX-CA

High-performance color mark sensor



E3NX-CA

High-performance color mark sensor



E3NX-MA

Smart Fiber Amplifier Units



E3NX-FA

High-performance digital fiber amplifier



E3X-NA

Digital fiber amplifier with potentiometer adjustment

Downloads

CAD Library



E32-LT/LD Hex-shaped Fiber Unit Brochure

EN PDF 6.35 MB



EAC Mark removal Discontinuation Notice

EN PDF 221 KB



Fiber Sensor Selection Selection Guide

EN PDF 16.2 MB

