




Connectors > Rectangular Connectors > Standard Rectangular Connectors > Glow Wire GRACE INERTIA Plug



Connector Product Type: **Housing**  
Connector & Housing Type: **Plug**  
Termination Method to Wire & Cable: **Crimp**  
Connector System: **Wire-to-Board**  
Contact Mating Area Plating Material: **Tin (Sn)**

[All Glow Wire GRACE INERTIA Plug \(78\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Power Positions	8
Number of Signal Positions	8
Number of Positions	8
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------



Body Features

Primary Product Color	Blue
-----------------------	------

Contact Features

Multiple Contact Types	Without
Contact Type	Receptacle
Contact Mating Area Plating Material Thickness	.8 μm[31.49 μin]
Contact Mating Area Plating Material	Tin (Sn)
Contact Retention Within Housing	With
Contact Current Rating (Max)	4 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Material	Nylon 6/6 GF
Centerline (Pitch)	3.3 mm[.129 in]

Dimensions

Wire Size	24 – 20 AWG
Row-to-Row Spacing	5.2 mm[.205 in]

Usage Conditions

Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Identification Marking

Circuit Identification Feature	Without
--------------------------------	---------

Industry Standards

Glow Wire Rating	GWT 750°C (Without Flame)
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Method	Bag
Packaging Quantity	1500



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # CAT-G7534-T669  
GRACE INERTIA TPA



TE Part # 1871567-1  
GIC 3.3 PLUG HOUSING 6POS 1ROW




TE Part # CAT-G7534-P729A  
Glow Wire GRACE INERTIA Plug


Also in the Series | GRACE INERTIA 3.3



Connector Contacts(3)



Connector Hardware(15)



PCB Headers & Receptacles(36)




Power Contacts(3)



Rectangular Connector Housings(34)



Rectangular Power Connectors(70)



Wire-to-Board Headers & Receptacles (36)

Customers Also Bought



TE Part #4-1123823-1  
EP 1P PLUG RED




TE Part #1565084-1  
GRACE INERTIA CONNECTOR 3.5 6P




TE Part #CAT-P8704-P729  
STD Temp Power Key Plug



TE Part #917701-1  
2.5 SIGNAL DBL LOCK DLP 5P



TE Part #6-1376387-2  
5.0 POWER KEY CONN.6P HDR ASSY



TE Part #917725-1  
2.5 SIGNAL D/LOCK HDR ASSY 5P



TE Part #3-1123823-1  
EP IP PLUG BLUE



TE Part #1827387-1  
GIC 3.3 PLUG HOUSING 8P

Documents

Product Drawings  
GIC 3.3 PLUG HOUSING 8P  
English

CAD Files  
Customer View Model  
ENG\_CVM\_CVM\_2-1827387-3\_E.2d\_dxf.zip  
English  
3D PDF



3D

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1827387-3\\_E.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_2-1827387-3\\_E.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

Japanese

[GRACE INERTIA CONNECTOR 3.3 CONTACT](#)

Japanese

Agency Approvals

[UL Report](#)

English