

Chains & sprockets	Wear strips	Side guide brackets & accessories	Levelers
Modular belts & sprockets	Chain & belt return systems	Frame & structure supports	Bearing supports
Curves & tracks	Side guide solutions	Miscellaneous products	Related information

11210a


828

www.SystemPlastSmartGuide.com

STRAIGHT RUNNING CHAINS



Click here for related information.



- High load capacity
- Zero gap


NG® evo Engineered Plastic Material

Longest life
Lowest friction
Good chemical resistance
High abrasion resistance
Approved for direct food contact
Less dust than with acetal chains
More.....

Features:

- Standardization
- Identical sprockets as sideflexing chains
- Standard conveyor construction
- High load capacity
- Particularly suitable for accumulation tables as well as for pressure-less combiners
- Improved product stability
- Reduced gap between adjacent tracks
- Better topplate flatness in the hinge area

Pin material: Austenitic steel



ITEM DESCRIPTION	MATERIAL PLATE	BREAKING LOAD		WIDTH L		WEIGHT	
		N	lbs	mm	in	Kg/m	lbs/ft.
NGE828-K325	NGE Grey Blue	5400	1200	82,5	3 ¼	1,1	0.7
NGE828-K330				83,8	3 19/64	1,2	0.8
LF828-K325	LF Brown	6000	1350	82,5	3 ¼	1,1	0.7
LF828-K330				83,8	3 19/64	1,2	0.8