



ENGLISH

Datasheet

Stock No: 811-4378

RS Pro BASEC 3 Core Grey Unscreened 3183Y Solid PVC Power Cable H05VV-F, 1.5 mm² CSA 15 A, 300 V, 500 V



Image representative of range

Product Details

BASEC approved H05VVF/3183Y 3 Core Cable

Flexible, 3 core cable with fine stranded copper conductors.

Features and Benefits

- PVC sheath
- PVC insulation

Applications

- Household applications
- Covered, dry, steamed and humid areas where low mechanical stress exists

Flexible PVC Cable

Specifications:

Number of Cores	3
Cross Sectional Area	1.5 mm ²
Sheath Colour	Grey
Current Rating	15 A
Voltage Rating	300 V, 500 V
Outer Diameter	9.4mm
Sheath Material	Polyvinyl Chloride PVC
Harmonised Code	H05VV-F
Type	3183Y
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+70°C
Screened/Unscreened	Unscreened
Conductor Strand Type	Solid
Conductor Resistance	13.3 Ω/km
Number of Strands	30
Standards Met	BASEC
Core Strands	30/0.25 mm
Size of Strands	0.25 mm
Insulation Material	PVC Type T11 to BS7655
American Wire Gauge	15 AWG
Conductor Material	Copper