

SIEMENS

Product data sheet

6ES7215-1BG31-0XB0


SIMATIC S7-1200, CPU 1215C,
 COMPACT CPU, AC/DC/RELAY,
 2 PROFINET PORT,
 ONBOARD I/O: 14 DI 24V DC;
 10 DO RELAY 2A, 2 AI 0-10V DC,
 2 AO 0-20MA DC,
 POWER SUPPLY: AC 85 - 264 V AC AT 47 - 63 HZ,
 PROGRAM/DATA MEMORY: 100 KB

General information	
Engineering with	
Programming package	As of STEP 7 V11.0 SP2
Supply voltage	
120 V AC	Yes
230 V AC	Yes
permissible range, lower limit (AC)	85 V
permissible range, upper limit (AC)	265 V
Line frequency	
Frequency of the supply voltage	47 Hz
Frequency of the supply voltage	63 Hz
Input current	
Current consumption (rated value)	100 mA at 120 V AC; 50 mA at 240 V AC
Inrush current, max.	20 A ; at 264 V
Output current	

Current output to backplane bus (DC 5 V), max.	1600 mA ; Max. 5 V DC for SM and CM
Power losses	
Power loss, typ.	12 W
Memory	
Usable memory for user data	100 kbyte
Work memory	
integrated	100 kbyte
expandable	No
Load memory	
integrated	4 Mbyte
Backup	
present	Yes ; (maintenance-free)
without battery	Yes
CPU processing times	
for bit operations, min.	0.085 μ s ; / instruction
for word operations, min.	1.7 μ s ; / instruction
for floating point arithmetic, min.	2.5 μ s ; / instruction
CPU-blocks	
Number of blocks (total)	DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used
OB	
Number, max.	Limited only by RAM for code
Data areas and their retentivity	
retentive data area in total (incl. times, counters, flags), max.	10 kbyte
Flag	
Number, max.	8 kbyte ; Size of bit memory address area
Address area	
I/O address area	
I/O address area, overall	1024 bytes for inputs / 1024 bytes for outputs
Process image	
Inputs, adjustable	1 kbyte

Outputs, adjustable	1 kbyte
Hardware configuration	
Number of modules per system, max.	3 comm. modules, 1 signal board, 8 signal modules
Time of day	
Clock	
Hardware clock (real-time clock)	Yes
Deviation per day, max.	+/- 60 s/month at 25 °C
Backup time	480 h ; Typical
Digital inputs	
Number/binary inputs	14 ; integrated
of which, inputs usable for technological functions	6 ; HSC (High Speed Counting)
integrated channels (DI)	14
m/p-reading	Yes
Number of simultaneously controllable inputs	
all mounting positions	
up to 40 °C, max.	14
Input voltage	
Rated value, DC	24 V
for signal "0"	5 V DC at 1 mA
for signal "1"	15 V DC at 2.5 mA
Input current	
for signal "1", typ.	1 mA
Input delay (for rated value of input voltage)	
for standard inputs	
Parameterizable	Yes ; 0.2, 0.4, 0.8, 1.6, 3.2, 6.4, and 12.8 ms, selectable in groups of four
at "0" to "1", min.	0.2 ms
at "0" to "1", max.	12.8 ms
for interrupt inputs	
Parameterizable	Yes
for counter/technological functions	
Parameterizable	Yes ; Single phase : 3 at 100 kHz & 3 at 30 kHz, differential: 3 at 80 kHz & 3 at 30 kHz
Cable length	

Cable length, shielded, max.	500 m ; 50 m for technological functions
Cable length unshielded, max.	300 m ; For technological functions: No
Digital outputs	
Number/binary outputs	10 ; Relay
integrated channels (DO)	10
Functionality/short-circuit strength	No ; to be provided externally
Switching capacity of the outputs	
with resistive load, max.	2 A
on lamp load, max.	30 W DC; 200 W AC
Output delay with resistive load	
"0" to "1", max.	10 ms ; max.
"1" to "0", max.	10 ms ; max.
Switching frequency	
of the pulse outputs, with resistive load, max.	1 Hz
Relay outputs	
Number of relay outputs	10
Number of operating cycles, max.	mechanically 10 million, at rated load voltage 100,000
Cable length	
Cable length, shielded, max.	500 m
Cable length unshielded, max.	150 m
Analog inputs	
Integrated channels (AI)	2 ; 0 to 10 V
Number of analog inputs	2
Input ranges	
Voltage	Yes
Input ranges (rated values), voltages	
0 to +10 V	Yes
Input resistance (0 to 10 V)	≥100k ohms
Cable length	
Cable length, shielded, max.	100 m ; twisted and shielded
Analog outputs	
Integrated channels (AO)	2 ; 0 to 20mA
Number of analog outputs	2

Cable length	
Cable length, shielded, max.	100 m ; Shielded, twisted wire pair
Analog value creation	
Integrations and conversion time/ resolution per channel	
Resolution with overrange (bit including sign), max.	10 bit
Integration time, parameterizable	Yes
Conversion time (per channel)	625 µs
Encoder	
Connectable encoders	
2-wire sensor	Yes
1st interface	
Type of interface	PROFINET
Physics	Ethernet
Isolated	Yes
Automatic detection of transmission speed	Yes
Autonegotiation	Yes
Autocrossing	Yes
Functionality	
PROFINET IO Controller	Yes
Communication functions	
S7 communication	
supported	Yes
as server	Yes
as client	Yes
Open IE communication	
TCP/IP	Yes
ISO-on-TCP (RFC1006)	Yes
UDP	Yes
Web server	
supported	Yes
User-defined websites	Yes
Test commissioning functions	
Status/control	

Status/control variable	Yes
Variables	Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters
Forcing	
Forcing	Yes
Diagnostic buffer	
present	Yes
Integrated Functions	
Number of counters	6
Counter frequency (counter) max.	100 kHz
Frequency meter	Yes
controlled positioning	Yes
PID controller	Yes
Number of alarm inputs	4
Number of pulse outputs	4
Galvanic isolation	
Galvanic isolation digital inputs	
Galvanic isolation digital inputs	500 V AC for 1 minute
between the channels, in groups of	1
Galvanic isolation digital outputs	
Galvanic isolation digital outputs	Relay
between the channels	No
between the channels, in groups of	2
Permissible potential difference	
between different circuits	500 V DC between 24 V DC and 5 V DC
EMC	
Interference immunity against discharge of static electricity	
Interference immunity against discharge of static electricity acc. to IEC 61000-4-2	Yes
Test voltage at air discharge	8 kV
Test voltage at contact discharge	6 kV
Interference immunity to cable-borne interference	
on the supply lines acc. to IEC 61000-4-4	Yes

Interference immunity on signal lines acc. to IEC 61000-4-4	Yes
Surge immunity	
on the supply lines acc. to IEC 61000-4-5	Yes
Immunity against conducted interference induced by high-frequency fields	
Interference immunity against high-frequency radiation acc. to IEC 61000-4-6	Yes
Emission of radio interference acc. to EN 55 011	
Emission of radio interferences acc. to EN 55 011 (limit class A)	Yes ; Group 1
Emission of radio interference acc. to EN 55 011 (limit class B)	Yes ; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011
Degree and class of protection	
IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
cULus	Yes
C-TICK	Yes
FM approval	Yes
Marine approval	Yes
Ambient conditions	
Operating temperature	
Min.	-20 °C
max.	60 °C
vertical installation, min.	-20 °C
vertical installation, max.	50 °C
horizontal installation, min.	-20 °C
horizontal installation, max.	60 °C
Storage/transport temperature	
Min.	-40 °C
max.	70 °C
Air pressure	

Operation, min.	795 hPa
Operation, max.	1080 hPa
Storage/transport, min.	660 hPa
Storage/transport, max.	1080 hPa
Relative humidity	
Operation, max.	95 % ; no condensation
Vibrations	
Vibrations	2G wall mounting, 1G DIN rail
Operation, checked according to IEC 60068-2-6	Yes
Shock test	
checked according to IEC 60068-2-27	Yes ; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms
Climatic and mechanical conditions for storage and transport	
Climatic conditions for storage and transport	
Free fall	
Drop height, max. (in packaging)	0.3 m ; five times, in dispatch package
Temperature	
Permissible temperature range	-40 °C to +70 °C
Mechanical and climatic conditions during operation	
Climatic conditions in operation	
Temperature	
Min.	-20 °C
max.	60 °C
Air pressure acc. to IEC 60068-2-13	
Permissible air pressure	1080 to 795 hPa
Permissible operating height	-1000 to 2000 m
Pollutant concentrations	
SO ₂ at RH < 60% without condensation	SO ₂ : < 0.5 ppm; H ₂ S: < 0.1 ppm; RH < 60% condensation-free
Configuration	
programming	
Programming language	
LAD	Yes
FBD	Yes

SCL	Yes
Cycle time monitoring	
adjustable	Yes
Dimensions	
Width	130 mm
Height	100 mm
Depth	75 mm
Weight	
Weight, approx.	550 g
Status	Sep 17, 2012