



Sliver for SFF-TA-1002

TE Internal #: 2292055-1

TE Sliver, Cable Plug Assembly, Right Angle, Cable-to-Board, 50 Position, Surface Mount, Sliver for SFF-TA-1002, Internal I/O Connectors

[View on TE.com >](#)

Connectors > PCB Connectors > Internal I/O Connectors



Internal I/O Connector Type: **TE Sliver**
Connector Mates With: **Cable Plug Assembly**
PCB Mount Orientation: **Right Angle**
Connector System: **Cable-to-Board**
Number of Positions: **50**

Features

Product Type Features

Connector & Contact Terminates To	Printed Circuit Board
Internal I/O Connector Type	TE Sliver
Connector Mates With	Cable Plug Assembly
Connector System	Cable-to-Board

Configuration Features

Number of Rows	2
PCB Mount Orientation	Right Angle
Number of Positions	50

Contact Features

PCB Contact Termination Area Plating Material	Tin
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Gold (Au)
Contact Base Material	Copper Alloy
Contact Current Rating (Max)	.9 A



Contact Mating Area Plating Material Thickness	.762 μm[30 μin]
--	-----------------

Termination Features

Termination Method to PCB	Surface Mount
---------------------------	---------------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	.6 mm[.023 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 85 °C[-67 – 185 °F]
-----------------------------	---------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 2821752-2
SLIVER C/A, 50P, STR TO R/A,25GHZ, 100OHM



TE Part # 2821744-2
SLIVER C/A, 50P, STR TO R/A, 25GHZ 85OHM



TE Part # 2821742-1
SLIVER C/A, 50P, STR TO STR, 25G, 85OHM



TE Part # 2820397-2
SLIVER C/A, 50P, STR TO STR, 10GHZ, 85OHM



TE Part # 2820399-2
SLIVER C/A, 50P, R/A TO R/A, 10GHZ, 85OHM



TE Part # 2820399-1
SLIVER C/A, 50P, R/A TO R/A, 10GHZ, 85OHM



TE Part # 2821747-2
SLIVER C/A, 50P, STR TO STR,10GHZ, 100OHM



TE Part # 2821751-2
SLIVER C/A, 50P, R/A TO R/A,25GHZ, 100OHM



TE Part # 2821743-2
SLIVER C/A, 50P, R/A TO R/A, 25GHZ 85OHM



TE Part # 2821748-2
SLIVER C/A, 50P, R/A TO R/A,10GHZ, 100OHM



TE Part # 2821638-1
SLIVER C/A, 50P, STR TO R/A, 10GHZ, 85OHM



TE Part # 2821750-2
SLIVER C/A, 50P, STR TO STR,25GHZ, 100OHM



TE Part # 2821751-1
SLIVER C/A, 50P, R/A TO R/A,25GHZ, 100OHM



TE Part # 2821638-2
SLIVER C/A, 50P, STR TO R/A, 10GHZ, 85OHM



TE Part # 2821752-1
SLIVER C/A, 50P, STR TO R/A,25GHZ, 100OHM



TE Part # 2821743-1
SLIVER C/A, 50P, R/A TO R/A, 25GHZ 85OHM



TE Part # 2821749-1
SLIVER C/A, 50P, STR TO R/A,10GHZ, 100OHM



TE Part # 2821748-1
SLIVER C/A, 50P, R/A TO R/A,10GHZ, 100OHM




TE Part # 2821742-2
SLIVER C/A, 50P, STR TO STR, 25G, 85OHM




TE Part # 2317815-1
CABLE PLUG KIT, SLIVER 50P,


Also in the Series | Sliver for SFF-TA-1002



Connector Hardware(1)




Internal I/O Cable Assemblies(105)



Internal I/O Connectors(133)


Customers Also Bought



TE Part #2170359-1
INV MJ, 1X4, PNL GRD




TE Part #2301995-1
RJ45 JACK INT. MAG. 1GB 1X1 VERT.



TE Part #5960092001
TFER-1-1/4-X-STK



TE Part #2204535-1
ELCON MINI 2X3P STACKED RA
HEADER, SOLDER




TE Part #2041126-1
MODULAR JACK, RJ45, SMT TYPE, AU:
6u"



TE Part #6-1734324-7
RJ45 w/ Y/GO LED PAL GND T&R 30u"




TE Part #2169259-1
SFP+ 1x6 Cage Assy, Extended H



TE Part #5960072006
TFER-3/4-X-STK



TE Part #2007251-1
SFP+ 1x6 Cage Assembly



TE Part #2204535-8
ELCON MINI 1X3P LONGER RA
HEADER, SOLDER

Documents

Product Drawings
RECEPTACLE ASSY RA 50 POSN MBC
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_2292055-1_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_2292055-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_2292055-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Sliver Internal Cabled Interconnect Solutions Brochure \(Chinese\)](#)

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English