



## Part Number: URM43

### COAX URM43 PVC

#### Product Description

COAX [0.9/2.95] URM43 PVC

#### Technical Specifications

##### Product Overview

Environmental Space:	Indoor - Euroclass Eca
Suitable Applications:	Coaxial communication cable based on BS2316

##### Physical Characteristics (Overall)

###### Conductor

Stranding	Material	Nominal Diameter	No. of Coax
Solid	BC - Bare Copper	0.9 mm	1

Conductor Count:	1
Conductor Size:	20 AWG

###### Insulation

Type	Material	Nominal Diameter	Diameter +/- Tolerance
Dielectric	Polyethylene	2.95 mm	0.15 mm

###### Outer Shield Material

Type	Material	Coverage [%]	Nominal Diameter	Coverage +/- Tolerance
Braid	BC - Bare Copper	91 %	3.63 mm	4 %

###### Outer Jacket Material

Material	Nominal Diameter	Diameter +/- Tolerance
PVC - Polyvinyl Chloride	5 mm	0.15 mm

OuterJacket1, Table Note:	According to European Standard HD 624
---------------------------	---------------------------------------

##### Construction and Dimensions

Min Elongation at Breakof Jacket:	150 %
Min Tensile Strength of Jacket:	12.5 MPa

##### Electrical Characteristics

###### Conductor DCR

Max. Conductor DCR
28 Ohm/km

###### Capacitance

Nom. Capacitance	Capacitance Tolerance
98 pF/m	5 pF/m

###### Impedance

Nominal Characteristic Impedance	Nominal Characteristic Tolerance	Regularity of Impedance
50 Ohm	2 Ohm	Min. 40 dB

## High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
100 MHz	13 dB/100m
200 MHz	18.7 dB/100m
300 MHz	23.2 dB/100m
600 MHz	33.8 dB/100m
1000 MHz	44.6 dB/100m

## Delay

Nominal Velocity of Propagation (VP) [%]
66 %

## High Freq

Frequency [MHz]	Min. RL (Return Loss) [dB]
5 - 30 MHz	20 dB
30 - 470 MHz	20 dB
470 - 1000 MHz	18 dB

High Freq Table Note: In each frequency band, 3 peak values up to 4 dB lower are allowed

## Voltage

Voltage Rating [V]
4000 DC / 2000 V RMS

## Temperature Range

Installation Temp Range:	-5°C To +50°C
Storage Temp Range:	-40°C To +70°C
Operating Temp Range:	-40°C To +70°C

## Mechanical Characteristics

Min Bend Radius (W/o Pulling Strength):	25 mm
Crush Resistance:	Max. 1% (load of 700N) N

## Standards

CPR Euroclass:	Eca
GENELEC Compliance:	EN 50289
Series Type:	UR Series
Other Specification:	BS2316

## Applicable Environmental and Other Programs

EU RoHS Compliance Date (yyyy-mm-dd):	2005-10-31
---------------------------------------	------------

## Flammability, LS0H, Toxicity Testing

ISO/IEC Flammability:	IEC 60332-1-2
-----------------------	---------------

## Part Number

### Variants

Item #	Color	Length
URM43.00500	Black	500 m
URM43.01100	Black	100 m

## History

Revision Number:	1
------------------	---

© 2019 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product

Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.