

## 9650FTP250P64

EAN 4031582314250

Swivel castor, housing and plate steel-welded, bright zinc plated, blue passivated, sealed swivel bearing with dual purpose bearing and tapered roller bearing, threaded king pin and locking nut secured, grease nipple, wheel axle with nut, plate fitting. Wheel centre made of cast iron, Tread: Polyurethane, casted, precision ball bearing



BETTER MOBILITY. BETTER LIFE.



Picture may differ from original product


### Technical Data

Wheel diameter	250 mm
Width of Tread	80 mm
Size of Plate	175 x 140 mm
Plate hole centres	140 x 105 mm
Plate hole	15 mm
Offset	65 mm
Swivel Interference	380 mm
Overall height	305 mm
Temperature	- 20 / + 60 °C
Standard	EN 12533
Weight	19.977 kg
Swivel Radius	190 mm
Hardness of tread	Shore A 92
Load capacity	1700 kg
Load capacity (static)	3400 kg


### Advantages at a glance

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

### Dimensions



### Structure & Mounting





BETTER MOBILITY. BETTER LIFE.

## 9650FTP250P64

EAN 4031582314250

### Structure & Mounting

---

