Worry Less and Do More

Eurotherm nanodac™ Recorder/Controller

High integrity graphical data recording aids statutory compliance across regulated industries.

World class PID control for greater performance and process reliability



Product at a glance

We combined our in depth knowledge of stringent data security requirements of regulated industries with our control expertise in specialist applications such as cascade control, sterilization and carbon control to bring you world class recording and PID control in a space-saving, small box with a superb full color display.

The recording functionality within the nanodac instrument reflects our understanding of the requirements of capturing and storing electronic data. We understand that different applications have different needs and so the nanodac recorder can store your information, either in open CSV format or in a tamper resistant, check summed format to better maintain data integrity. Whichever format you choose for your process, we have the tools to help you keep this data more secure, get it to the place you need, and in the format you require. Digital batch recording and electronic signatures helps simplify reporting and the audit process .This aids compliance with GAMP, NADCAP and HACCP/HARPC requirements.

Add to this our commitment to technological innovation, constant reinvestment in research and development, and a team of engineers who understand your process requirements and you will find in Eurotherm a partner able to flex with the demands of your business as the regulatory and audit landscape changes.

- Tamper resistant data recording methodology trusted by auditors
- Electronic signing and authorisation compliant with 21CFR Part 11
- · Powerful batch functionality
- Eurotherm PID algorithm with 2 control loops
- · Cascade control with advanced autotune
- Dual programmer
- · High accuracy universal inputs
- Graphical wiring
- USB removable data storage facility
- Modbus TCP/IP Master/Slave
- EtherNet/IP Client or Server
- BACnet Slave
- Sterilizer Application Block
- Relative Humidity Application Block
- Steam Flow Application Block
- Zirconia Probe Application Block
- Multi-language support
- · Compact design

nanodac[™] Specification

General Hardware and Software

| I/O Types | | |
|-------------------------|---|--|
| Analog inputs | Four standard (eight if dual input enabled) | |
| Digital inputs | Two as standard, One optional | |
| Digital (logic) outputs | Two optional | |
| Relay outputs | Two as standard, two optional | |
| DC outputs | Three optional | |

| Ethernet Communications | | |
|-------------------------|--|--|
| Ethernet Communications | 10/100BASE-T Ethernet (IEEE802.3) | |
| Protocols | Modbus TCP Slave (default), Options for Modbus TCP Master, Ethernet/IP Client or Server, BACnet, FTP | |
| Cable type | Category 5 Shielded | |
| Maximum Cable length | 100 meters (110 yards) | |
| Connector Type | RJ45 (Green LED illuminated = Link Connected; Amber LED Flashing = Link Activity) | |
| Network Addressing | DHCP or Fixed (Static) IP Addressing | |

| USB Port | | |
|-----------------------|--|--|
| Number of ports | One at rear of instrument | |
| Standard | USB1.1 | |
| Transmission speed | 1.5Mbits/s (low speed device) | |
| Maximum current | <100mA | |
| Peripherals supported | Memory stick (8GB max), Barcode scanner, QWERTY keyboard | |

| Battery Backup | | |
|-----------------------|--|--|
| Stored Data | Time and Date only | |
| Support Time | Minimum of 1 years with unit unpowered | |
| Replacement period | Three years Typical | |
| Temperature Stability | 0 to 55°C ≤±3.5ppm | |
| RTC Aging | First year to 10 years < 5ppm | |
| Battery Type | Lithium/poly-carbonmonofluoride | |

| Operator Interface | | |
|--------------------|--|--|
| Integrated Display | 3.5" color TFT | |
| | (320 pixels wide x 240 pixels high) | |
| User interface | Four navigation push buttons (Page, Scroll, Lower and Raise) | |


| Data Recording | | |
|---------------------------|--------------------------------------|--|
| Sample Rate | 8Hz (125ms) | |
| Trend Display update rate | 8Hz (125ms) | |
| Recording Groups | 1 | |
| Display points | 6 | |
| Recording points | up to 34 (with Modbus Master Option) | |
| Data Storage | 50MB | |

nanodacTM Specification

Power supply, Isolation, Environmental and Compliance

| Power Specifications | |
|---|---|
| Supply voltage | Standard: 100 to 230V ac ±15% at 48 to 62Hz |
| | Low voltage Option: 24V ac (+10% -15%) at 48 to 62Hz, or 24V dc (+20% -15%) |
| Power dissipation | 9W (max.) |
| Fuse type | No internal fuse fitted |
| Interrupt Protection (Standard unit) | Holdup >20ms at 85V RMS supply voltage |
| Interrupt Protection (Low voltage unit) | Holdup >20ms at 20.4V RMS supply voltage |

| Control | | |
|--------------------|---|--|
| Control Loops | Two, plus advanced control | |
| | (cascade) loop | |
| Control Types | On/Off, PID, VPU, Cascade | |
| | (Advanced Loop) | |
| Advance Features | | |
| Application Blocks | Zirconia, Relative Humidity, Steriliser, Steam/Mass Flow | |
| Batch | Single Batch, six Batch Fields | |
| Auditor | Up to 25 users with individual | |
| | username, password and | |
| | permissions | |



| Isolation | details |
|-----------|---------|
| | |

| Environmental Specifications, Approvals and Compliance | | | |
|--|---------------------------|---|--|
| Operating temperature | | 0 to 55°C | |
| Storage temperature | | -20 to +70°C, max rate of change 1°C per minute | |
| Operating humidity | | 5% to 85% RH non condensing | |
| Storage humidity | | 5% to 85% RH non condensing | |
| Front of panel protection | n | Standard: IP65, Washdown: IP66, NEMA12 | |
| Back of panel protection | n | IP10 (International) | |
| Shock/vibration | | To BS EN61131-2 (5 to 150 Hz. at 1g; 1 octave per min.) | |
| Altitude | | <2000 meters | |
| Atmosphere | | Not suitable for use in explosive or corrosive atmospheres | |
| Electrical safety | | BS EN61010-1 (installation category II; Pollution degree 2) | |
| Electromagnetic compatibility (EMC) | Emissions (Standard unit) | BS EN 61326 Class B – Light industrial | |
| | Emissions | DO FALOMORO Oleve A. Harve Park at Park | |
| (Low voltage unit) | | BS EN 61326 Class A – Heavy industrial | |
| | Immunity | BS EN 61326 Industrial | |

| Approvals and Compliance | |
|--------------------------|------------------------------|
| General | CE, UL and EN61010 |
| PV Input | AMS2750E compliant |
| RoHS | EU; China |
| Packaging | BS EN61132-2 section 2.1.3.3 |

nanodac[™] Specification

Built in I/O

Analog Inputs (An In 1-4)

| Analog Inputs General | |
|------------------------------|--|
| Number of inputs | Four |
| Input types | dc volts, dc mV, dc mA (external shunt required), thermocouple, linear ohms, RTD (2-wire and 3-wire) |
| Input type mix | Freely configurable |
| Update rate | 125ms max. |
| Conversion method | 16 bit delta sigma |
| Input ranges | See individual tables |
| Mains rejection (48 to 62Hz) | > 95dB series mode >179dB common mode |
| Common mode voltage | 250V ac max. |
| Series mode voltage | 280mV at lowest range; 5V peak to peak at highest range |
| Input impedance | $>$ 100M Ω (40mV, 80mV, 2V ranges only) $667k\Omega \text{ for input} < 5.6\text{V, } 62.5k\Omega $ for input $>$ 5.6V (10V range only) |
| Overvoltage protection | ±30V RMS (continuous) ±200V pk-pk between terminals (transient <1ms) |
| Sensor break detection | ac sensor break on each input giving quick response with no associated dc offset Recognition time<3 seconds Minimum break resistance: $5k\Omega$ for 40mV and 80mV ranges; $12.5k\Omega$ for 2V and 10V ranges |
| Isolation | 300V RMS or dc (double insulation) channel to channel 300V RMS or dc (double insulation) channel to processor electronics 300V RMS or dc (single insulation) channel to ground |
| Dielectric strength | BS EN 61010, 1 minute type test 2500V ac channel to channel 1500V ac channel to ground |

Voltage Inputs

| mV and | mV and V inputs | | | |
|---------|-----------------|------------|-------------------------|--------------|
| Low | High | Resolution | Calibration accuracy | Temperature |
| range | range | Resolution | (instrument at 25°C) | performance |
| -40mV | +40mV | 1.9µV | $4.6\mu V + 0.053\%$ of | 13ppm of |
| -401110 | ±40IIIV | 1.9μν | reading | input per °C |
| -80mV | +80mV | 3.2µV | $7.5\mu V + 0.052\%$ of | 13ppm of |
| -001110 | 1001117 | J.Ζμν | reading | input per °C |
| -2V | +2V | 0211/ | $420\mu V + 0.044\%$ of | 13ppm of |
| -ZV | TZV | 82µV | reading | input per °C |
| -3V | +10V | 500µV | 1.5mV + 0.063% of | 45ppm of |
| -5v | 1100 | σοσμν | reading | input per °C |

Thermocouple Inputs

| Thermocouple Inputs | |
|------------------------------|--|
| Temperature scale | ITS90 |
| CJC types | Off, internal, external, remote |
| Remote CJC source | Any analog input channel |
| Internal CJC accuracy | <1°C max, with instrument at 25°C |
| Internal CJC rejection ratio | 40:1 from 25°C |
| Upscale/downscale drive | High, low or none independently configurable for each channel's sensor break detection |

| Thermocouple Types | | | | |
|----------------------|--------------------|------------------------------|------------------------|--|
| T/C type | Overall range (°C) | Standard | Linearization accuracy | |
| | | | 0 to 400°C = 1.7°C | |
| В | 0 to +1820 | IEC584.1 | 400 to 1820°C = | |
| | | | 0.03°C | |
| С | 0 to +2300 | Hoskins | 0.12°C | |
| D | 0 to +2495 | Hoskins | 0.08°C | |
| Е | -270 to +1000 | IEC584.1 | 0.03°C | |
| G2 | 0 to +2315 | Hoskins | 0.07°C | |
| J | -210 to +1200 | IEC584.1 | 0.02°C | |
| K | -270 to +1372 | IEC584.1 | 0.04°C | |
| L | -200 to +900 | DIN43710:1985 (to IPTS68) | 0.02°C | |
| N | -270 to +1300 | IEC584.1 | 0.04°C | |
| R | -50 to +1768 | IEC584.1 | 0.04°C | |
| S | -50 to +1768 | IEC584.1 | 0.04°C | |
| Т | -270 to +400 | IEC584.1 | 0.02°C | |
| U | -200 to + 600 | DIN43710:1985 | 0.08°C | |
| NiMo/NiCo | -50 to +1410 | ASTM E1751-95 | 0.06°C | |
| Platinel | 0 to +1370 | Engelhard | 0.02°C | |
| Mi/NiMo | 0 to +1406 | Ipsen | 0.14°C | |
| Pt20%Rh/ Pt40%/Rh | 0 to +1888 | ASTM E1751-95 | 0.07°C | |

nanodacTM Specification

Built in I/O

Current Inputs

mA input accuracy is based on the shunt value and voltage range. Standard mA selection uses -3 to 10V range, therefore use -3 to 10V range specifications.

| mA Inp | mA Inputs | | | |
|-----------|------------|----------------|---|--|
| Low range | High range | External shunt | Shunt accuracy | |
| 0 | 20mA | 1Ω to 1kΩ | Dependent on shunt selection. 0.1% of input for shipped 2.49Ω shunt. | |

| RTD Types | | | | |
|-----------|---------------|----------------------|---------------|--|
| RTD | Overall range | Standard | Linearization | |
| type | (°C) | Statituatu | accuracy | |
| Cu10 | -20 to +400 | General Electric Co. | 0.02 °C | |
| Cu53 | -70 to +200 | RC21-4-1966 | 0.01 °C | |
| JPT100 | -220 to +630 | JIS C1604:1989 | 0.01 °C | |
| Ni100 | -60 to +250 | DIN43760:1987 | 0.01 °C | |
| Ni120 | -50 to +170 | DIN43760:1987 | 0.01 °C | |
| Pt100 | -200 to +850 | IEC751 | 0.01 °C | |
| Pt100A | -200 to +600 | Eurotherm | 0.09 °C | |
| FLIOUA | -200 to 1000 | Recorders SA | 0.09 C | |

Resistance Inputs

| Linear | Linear Ohms Inputs | | | | |
|--------------|--------------------|------|--|--------------------------|--|
| Low range | High range | Res | Calibration accuracy (Instrument at 25°C) | Temperature performance | |
| 0Ω | 400Ω | 20mΩ | 120mΩ + 0.023% of reading | 25ppm of input per °C | |

Digital Inputs (Dig in A and Dig in B only)

| Contact Closure Input | | |
|------------------------------------|---------------------------------|--|
| Closed circuit sensing current | 5 5mA min to 6 5mA max | |
| (source) | 3.3IIIA IIIIII to 0.3IIIA IIIax | |
| Open circuit (inactive) resistance | >600Ω | |
| Closed circuit (active) resistance | <300Ω | |
| Update rate | 8ms max | |

RTD Inputs

| Pt100 Inputs | |
|-------------------------|---|
| Temperature scale | ITS90 |
| Maximum source | 200μΑ |
| current | |
| Range | 0 to 400Ω (–200 to +850°C) |
| Resolution | 0.05°C |
| Calibration accuracy | ±0.31°C ±0.023% of |
| | measurement in °C at 25°C ambient |
| Temperature coefficient | ±0.01°C/°C ±25ppm/°C |
| | measurement in °C from 25°C ambient |
| Measurement noise | 0.05°C peak-peak with 1.6s input filter |
| Linearity | 0.0033% (best fit straight line) |
| Lead resistance | 0 to 22Ω matched lead resistances |

Relay Outputs (O/P4 and O/P5 only)

| Form A N/O Relay Outputs | |
|---------------------------|--------------------------------|
| Contact switching power | 1A max at 240V RMS +/-15%, |
| (resistive) | 5mA min at 5V |
| Current through terminals | 1A |
| Isolation | 300V RMS or dc, double |
| | insulated from processor/comms |
| | electronics |
| Update rate | 8ms max |

nanodacTM Specification

Optional I/O

| Table A1 Output Options (OPT 1 to OPT 3) | | | | |
|--|-------|-------|--|--|
| OPT 1 | OPT 2 | OPT 3 | | |
| L | R | R | | |
| L | R | D | | |
| L | L | R | | |
| R | D | D | | |
| D | D | D | | |
| L | L | D | | |

Logic Input (Available in Opt 1 only)

| Active (current on) Contact Closure | | |
|-------------------------------------|-----------------------|--|
| Input current (input at 12V) | 0mA min to 44mA max | |
| Input current (input at 0V) | 6mA (steady state) to | |
| | 44mA (switch current) | |
| Open circuit input voltage | +11V to +13V | |
| Open circuit (inactive) resistance | >500Ω | |
| Closed circuit (active) resistance | <150Ω | |
| Update rate | 8Hz (125ms) max | |

Logic Outputs (Available in Opt 1 or Opt 2)

| Logic Output (current sourcing) | | |
|--|---|--|
| Voltage Output across terminal (current on) | +11V to +13V | |
| Voltage Output across terminal (current off) | 0mV to +300mV | |
| Short circuit output current (current on) | 6mA (steady state) to 44mA (switch current) | |
| Output source leakage current (current off) | 0μA to 100μA | |
| Update rate | 8Hz (125ms) max | |

Relay Output (Available in Opt 1, Opt 2 or Opt 3)

| Form A (N/O) Relay Outputs | | | | |
|----------------------------|----------------------------------|--|--|--|
| Contact switching power | Max 2A at 230V RMS ±15%; | | | |
| (resistive) | Min 100mA at 12V | | | |
| Current through terminals | 2A max | | | |
| Estimated mechanical life | >10,000,000 operations | | | |
| Update rate | 8Hz (125ms) max | | | |
| Isolation | 300V RMS or dc, double insulated | | | |
| | from processor electronics | | | |

DC Outputs (Available in Opt 1, Opt 2 or Opt 3)

| Voltage Output | | |
|--------------------------------|--------------------------------|--|
| Output range (current) | Configurable within 0 to 20mA | |
| Load resistance (current) | 500Ω min | |
| Calibration Accuracy (current) | <±100µA ±1% of reading | |
| Output range | Configurable within 0 to 10Vdc | |
| (voltage, Opt 3 only) | | |
| Load resistance | 500Ω min | |
| (voltage, Opt 3 only) | | |
| Calibration Accuracy | <±50mV ±1% reading | |
| (voltage, Opt 3 only) | | |
| Resolution | >11 bits | |
| Thermal Drift | <100ppm/°C | |
| Update Rate | 8Hz (125ms) max | |
| Isolation | 300V RMS or dc, double | |
| | insulated from processor | |
| | electronics | |

Standard I/O


| Fixed Dig InA/Dig InB (Contact Closure) | | | | |
|---|--------------------------|--|--|--|
| Short circuit sensing current source | 5.5mA (min); 6.5mA (max) | | | |
| Open circuit (inactive) resistance | 600Ω (min); ∞ (max) | | | |
| Closed circuit (active) resistance | 0Ω (min); 300Ω(max) | | | |

| Fixed Form A N/O Relay Outputs (O/P4 and O/P5) | | | | |
|--|---|--|--|--|
| Contact Switching Power | Max 1A at 230V RMS ±15%; Min | | | |
| (resistive) | 100mA at 12V | | | |
| Current through terminals | 1A max | | | |
| Estimated mechanical life | >10,000,000 operations | | | |
| Update Rate | 8Hz (125ms) max | | | |
| Isolation | 300V RMS or dc, double insulated from processor electronics | | | |

nanodac[™] Specification

Terminal Wiring Details

| No. of wires | Wire size | | Screw terminal torque | |
|---------------|---|--------------------------|-----------------------|----------------|
| ive. or wiles | mm ² | AWG | Nm | lb in |
| 1 wire | 0.205 to 2.08 mm ² | 24 to 14 AWG | 0.4Nm max | 3.54 lb in max |
| 2 wires | 0.205 to 1.31 mm ² (inclusive) | 24 to 16 AWG (inclusive) | 0.4Nm max | 3.54 lb in max |



Rear terminals


I/O Terminations


Termination details

The screw terminals accept wire sizes in the range:

Single wire 0.205 to 2.08mm2 (14 to 24 AWG) 2 wires 0.205 to 1.31mm2 (16 to 24 AWG) inclusive.

Screw terminals should be tightened to a torque not exceeding 0.4Nm (3.54 lb in).







Use copper conductors only.

The power supply input is not fuse protected.

This should be provided externally.

Each wire connected to LA, LB and LC must be less than 30 metres in length.








nanodac[™] Specification

Mechanical Details










nanodac™ Order Codes



Basic Product

NANODAC Graphical Recorder/

1 Supply Voltage

VH 100-230V ac ±15% at 48-62Hz
VL 24V ac (+10% –15%) at 48-62Hz, or 24V dc (+20% –15%)

2 Controller

X None (default)
C 2 Control loops
Advanced control loop
(includes 2 control loops)

3 Programmer

X None (default)
P Dual programmer

4 Output Options 1-2-3

LRR Logic/Relay/Relay (default)
LRD Logic/Relay/Iso DC output
LLR Logic/Logic/Relay
RDD Relay/Iso DC/Iso DC
Iso DC/Iso DC
LDD Logic/Iso DC/Iso DC
LDD Logic/Logic/Isso DC
LDD Logic/Logic/Isso DC

5 Application Blocks

XX None
ZC Zirconia
RH Humidity
ST Steriliser

6 Communications Protocol

TS Modbus TCP/IP slave (default)

TM Modbus TCP/IP master
ES EtherNet/IP client/server
BS BACNet Server (Slave)
BACNet Server (Slave) & Modbus TCP Master

7 Bezel

SV Silver (standard)
WD Wash down front

8 Toolkit Blocks

XXXXX None
BASIC Basic toolkit blocks

9 Operating Language

ENG English (default)
FRA French
GER German
ITA Italian
SPA Spanish

10 OEM Security

XXX None
OEM OEM Security enabled

Labels

XXXXX No custom labels

12 Special

XXXXX Default

13 Dual Input Channels

XX None
5 inputs enabled
6 inputs enabled
7 inputs enabled

14 Dual Thermocouple Support

XXX None
TC Dual T/C support enabled

8 inputs enabled

5 Batch

NONE None BATCH Batch enabled

16 Auditor Full (21CFR11)

NONE AFULL None Auditor Full (21CFR11) enabled

17 Steam Flow Calculations

XX None (Default)
Steam/Mass Flow
Calculations

Faraday Close, Durrington, Worthing, West Sussex BN13 3Pl Phone: + 44 (01903) 268500 Fax: + 44 (01903) 265982





Eurotherm.