

LGGB 2


SKF Biodegradable Bearing Grease

SKF LGGB 2 is a biodegradable, low toxicity, synthetic ester oil based grease, using a lithium-calcium thickener. Its special formulation makes it most suitable for applications where environmental contamination is a concern.

- Compliance with current regulations on toxicity and biodegradability
- Good performance in applications with steel-on-steel spherical plain bearings, ball bearings and roller bearings
- Good low temperature start-up performance
- Good corrosion inhibiting properties
- Suitable for medium to high loads

Typical applications:

- Agricultural and forestry equipment
- Construction and earthmoving equipment
- Mining and conveying equipment
- Water treatment and irrigation
- Locks, dams, bridges
- Linkages, rod ends



Technical data

Designation	LGGB 2/(pack size)
DIN 51825 code	KPE 2K-40
NLGI consistency class	2
Soap type	Lithium/calcium
Colour	Off white
Base oil type	Synthetic ester
Operating temperature range	-40 to +90 °C (-40 to +195 °F)
Dropping point DIN ISO 2176	>170 °C (>340 °F)
Base oil viscosity	
40 °C, mm ² /s	110
100 °C, mm ² /s	13
Penetration DIN ISO 2137	
60 strokes, 10 ⁻¹ mm	265–295
100 000 strokes, 10 ⁻¹ mm	+50 max. (325 max.)
Mechanical stability	
Roll stability, 50 hrs at 80 °C, 10 ⁻¹ mm	+70 max. (350 max.)

Corrosion protection	
Emcor: – standard ISO 11007	0–0
Water resistance	
DIN 51 807/1, 3 hrs at 90 °C	0 max.
Oil separation	
DIN 51 817, 7 days at 40 °C, static, %	0,3–3
Lubrication ability	
R2F, running test B at 120 °C	Pass at 100 °C (210 °F)*
Rolling bearing grease life	
ROF test L ₅₀ life at 10 000 r/min., hrs	>300 at 120 °C (250 °F)
EP performance	
Wear scar DIN 51350/5, 1 400 N, mm	1,8 max.
4-ball test, welding load DIN 51350/4, N	2 600 min.
Available pack sizes	
	420 ml cartridge
	5, 18, 180 kg
	SKF SYSTEM 24 (LAGD)

* Typical value




SKF lubricants offer major competitive advantages:

- Designed and tested to outperform under real conditions
- Product data include specific test results enabling a better selection
- Strict quality control of every production batch help ensure consistent performance
- Quality control allows SKF to offer a five-year shelf-life* from the date of production



Production processes and raw materials vastly influence grease properties and performance. It is virtually impossible to select or compare greases based only on their composition. Therefore, performance tests are needed to provide crucial information. In over 100 years, SKF has accrued vast knowledge about the interaction of lubricants, materials and surfaces.



This knowledge has led SKF, in many cases, to set industry standards in bearing lubricant testing. Emcor, ROF, ROF+, V2F, R2F and Bequiet are just some of the multiple tests developed by SKF to assess the performance of lubricants under bearing operating conditions. Many of them are widely used by lubricant manufacturers worldwide.

* SKF LGFP 2 food grade grease offers a two-year shelf-life from the date of production

© SKF is a registered trademark of the SKF Group.

© SKF Group 2013

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless prior written permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

PUB MP/P8 12049 EN · December 2013

