

## Description

CHROME SWIVEL BOLT HOLE CASTOR, GREY RUBBER 80mm, 70kg

## Part Number

**Swivel**  
145301400A

**Swivel with brake**  
145301420A



	Swivel	Swivel + Brake
Wheel Diameter ØD	80 mm	
Overall Height H	110 mm	
Center hole	12,5 mm	
Spacing between castor flanges	35 mm	
Offset F ±1	30 mm	30 mm
Axle Type	Bolt M8	
type de moyeu	2 Ball bearings	
Hub Length	33 mm	
Wheel Bore Diameter	8 mm	
Tread Width	25 mm	
Tread Width on the ground	21 mm	
Hardness Tread shore A ± 5	80	
Load capacity	70 Kg	
Weigth	0,41 kg	0,52 kg

### Castor Assembly :

Chrome-plated pressed steel, swivel on two rows of balls  
Upper row protected by plastic seal. Sheet metal thickness 2mm  
Total lock (wheel and swivel). Short steel brake pedal.  
Central bolt hole fitting

### Wheel :

Wheel center made of grey polypropylene RAL 7037  
Tread : Thermoplastic rubber, grey non marking. Two ball bearings.  
Chrome-plated steel threadguards.

### Features :

Silent and easy to push and pull which reduces the risk of injury and disorders to the individual using the product  
Attractively designed, shiny chrome.  
Easily accessible steel brake pedal  
Non-marking thermoplastic rubber tyre fitted  
Robust.